## **Style M Contacts**



## **Series 8485 – Special Contacts for Style M Connectors**

## HIGH POWER RECEPTACLE CONTACT FOR RECEPTACLE SERIES 8484

Variation	Termination	ØA*	Performance	Ordering Code
AIG [0.268] AIG [0.168] AIG [0.168] AIG [0.168]	Screw Ø3M	.114 (2.90) for .118 (3.00) PCB hole Note: set	40 Ampere max.	70 8485 0214 00 343
PRESS-FIT SECTION FOR PLATED HOLE 3.0MM DIA	Press-Fit	PCB hole spec drilled hole 3.1-0.02 finish hole 3.0+0.04-0.06	40 Ampere max.	70 8485 0314 00 343

NB: Please refer to page 49 for other special contacts and tools for Press-Fit Style M Connectors.