







SCHEMATIC



PUSH



P. C. B LAYOUT



Rated Voltage	DC30V 0.1A
Withstand Voltage	AC250V 1 minute
Contact Resistance	≤ 50 mΩ
Operating Force	160 ± 80gf
Insulation Resistance	≥ 100 MΩ DC250V
Soldering Process	Hand Soldering
Mechanical Life	100,000 cycles
Electrical Life	10,000 cycles
Soldering Temper	Hand soldering Wave soldering
Total Travel (TT)	2.5 ± 0.2 mm
Operating Temper	-25 °C ~ + 65 °C
Ambient Humidity Used	< 85%RH

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 3-21-12

Rev. 0

Unit: mm

Checked By: *G. Gold*

Title:

PUSH SWITCH

CW P/N:

GPBS800N