SPECIFICAIONS:

Rating: DC30V 1A;

Contact resistance:  $100m \Omega$  (Max.);

Insulation resistance: DC500V 100M  $\Omega$  (Min.); Withstand voltage: AC 1000V for 1 minute;

Operating force: 500±200gf; Life cycle: 20,000 cycles; Total Travel: 1.5±0.3mm.

MATERIAL:


Frame: PBT,UL rated:94V-2 Min.;

Cap: POM;


Terminal:Brass,Silver or Tin plated.


Function: ON(1-6)-OFF


Cap Color: Black




P.C.B.LAYOUT(BottomView)









**RoHS Compliant** 

INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Push Button Switch was Torch Switch in title. 6-05-12.

2 22 42

Date Drawn: 3-22-12

Rev. 1

Unit: mm

Checked G. Guld

Title:

**PUSH BUTTON SWITCH** 

CW P/N:

GPTS203211B