

155-05400

Oval Stud Mount Cable Tie, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg

Article Number: 155-05400

Part Number: 155-05400

Type: T50SOSSB5HEC



[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

[| Share](#)

[Base Data](#)

Part No.	155-05400
Type	T50SOSSB5HEC
Color	Black (BK)
Features	- Oval mount design pushes on easy by hand without the need for tools. - Design provides low insertion and high extraction force.
Application Method	The "soft push" mount allows it to be installed onto a weld stud without the use of any tools.
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Primarily designed for use in the automotive industry, these parts can be used in a wide variety of applications where 5mm weld studs or 5mm ISO bolts are used and cables need to be bundled and secured.
Variant	Outside Serrated

[Product Dimensions](#)

Min. Tensile Strength	50.0lbs / 170N
Length (L)	6.0" / 160mm
Width (W) (imperial)	0.19"
Width (W)	4.6mm
Height (H2)	0.63"
Min. Ø Bundle	0.04" / 1.0mm
Max. Ø Bundle	1.4" / 35.0mm
Min. Stud Length	11.0mm
Max. Stud Length	16.0mm
Thickness	1.35mm
Stud Ø	.20" / 5.0mm

[Material and Specifications](#)

- [Cable Ties](#)
- [Cable Ties with Fasteners](#)
 - [Arrowhead Push Mount Ties](#)
 - [Button Head Cable Ties](#)
 - [Edge Clip Cable Ties](#)
 - [Fir Tree Mount Cable Ties](#)
 - [Screw Mount Cable Ties](#)
 - [Stud Mount Cable Ties](#)
- [Cable Tie Tools](#)
- [Clamps and Clips](#)
 - [Heatshrink Moulded Shapes](#)
- [Mounts](#)
- [Heavy Duty Mounts](#)
- [Wire Connectors](#)
- [Wiring Duct](#)
- [Wiring Protection](#)
- [Labels, Printers and Software](#)
 - [Pre-Terminated Networking](#)
- [Copper Network Solutions](#)
- [Fiber Network Solutions](#)
- [Jacks and Wall Plates](#)
- [Racks - Cable Management](#)
- [Surface Raceway Systems](#)