

Home

Events

Careers

How To Buy

Contact

Products

Industries

Resources

News

About Us

▶ Cable Ties

▶ Cable Ties with Fasteners

▶ Cable Tie Tools

▶ Clamps and Clips

Heatshrink Moulded Shapes

▶ Mounts

▶ Heavy Duty Mounts

▶ Wire Connectors

▶ Wiring Duct

▶ Wiring Protection

▶ Labels, Printers and Software

Pre-Terminated Networking

▶ Copper Network Solutions

▶ Fiber Network Solutions

▶ Jacks and Wall Plates

▶ Racks - Cable Management

▶ Surface Raceway Systems

CTT60R0HIRC2

Compression Tie, 8" Long, 60lb Tensile Strength, PA66HIRHS, Black, 100/pkg

Article Number: 112-52108

Part Number: CTT60R0HIRC2

Type: CTT60R

➔ Base Data

Part No.	CTT60R0HIRC2
Type	CTT60R
Color	Black (BK)
Features	• High impact and heat stabilized cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration. • Head design contains clamping rails to provide full circumferential compression around bundles. • Bent tail allows for quick insertion into head.
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	The clamps are recommended for soft rubber hose applications including fuel, water, and air vacuum lines.
Variant	Inside Serrated

➔ Product Dimensions

Min. Tensile Strength	60.0lbs / 265.0N
Length (L)	8.0" / 205.0mm
Width (W) (imperial)	0.19"
Width (W)	4.7mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	1.8" / 45.0mm

➔ Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
CSA Certified	No
Flammability	UL94 HB
Material Specification	RoHS
Operating Temperature	-40 °F to +302 °F (-40 °C to +150 °C)
ROHS Conformity	
Specification	UL
UL Listed (US and Canada)	No

➔ Find a Distributor

➔ Order Samples

➔ Get Technical Drawings



 |

 Share

http://www.hellermannntyton.us/productDetail.aspx?lon=CTT60R0HIRC2&ref=search.aspx[11/7/2013 2:59:13 PM]