



TAG1-100

Dot Matrix, Self-Laminating Label, 1.9" X .75' X 3.19", 4 Across, White, 2500/pkg

Article Number: 595-01100

Part Number: TAG1-100

Type: TAG1

Base Data

Part No.	TAG1-100
Type	TAG1
Color	White (WH)
Features	• Tabtag Dot Matrix labels are specifically made for use in dot matrix printers for fast and easy printing. • Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.
Application Method	Labels are printed using a HellermannTyton thermal transfer printer and then applied by hand.
Color Marking Field	White (WH)
Mounting method	Pasting / Stick
Identification ETIM	
Self adhesive (Yes/No)	Yes
Typical Application	Used in applications where low to medium print volumes are needed and where simple alphanumeric texts are required. HellermannTyton self laminating wire markers can be used in industries ranging from automotive wire and cable, to wire harness and cable assembly applications. For problem-free printing, we recommend our easy to use windows based Tagprint PRO version 2.0 software program, which comes pre-loaded with all our standard label templates so you can start producing labels immediately.
Variant	Adhesive label
With label space ETIM	Yes

Product Dimensions

Length (L)	3.19" / 81.0mm
Core diameter from / to	9.9 - 19.70mm

Width (W) (imperial)	1.9"
Width (W)	48.0mm
Height (H)	0.75" / 19.05mm
Height (H2)	3.19" / 81.0mm
Min. Ø Bundle	.389" / 9.90mm
Max. Ø Bundle	.770" / 19.70mm
Min. Outside Ø	.389"
Min. Diameter Ø	9.9mm
Max. Outside Ø	.770" / 19.70mm
HR	50.80mm / 2.000"
Print Method	Dot-Matrix
Thickness	75.0µm
Thickness of Foil (µm)	75µm
Vertical Repeat	3.500" / 88.90mm
Width of Liner (WL)	241.30mm / 9.500"

Material and Specifications

Material	Type 100, self laminating Vinyl, white (WH)
Adhesive	Acrylic / Acryl
Adhesive Operating Temperature	-51 °F to +200 °F (-46 °C to +93 °C)
Curing Temperature	from +50 °F (from +10 °C)
Material Specification	RoHS
Operating Temperature	-51 °F to +200 °F (-46 °C to +93 °C)
ROHS Conformity	 RoHS
Specification	UL-Recognized

Logistic and Packaging

Packaging Type	pack
Pkg. Qty.	2500 / 2500
Carton Qty.	2500Pieces

EAN code	4031026175089
Labels per Column	4
Labels per Row	4
Labels per Sheet	12
Minimum Order Quantity	2500
UPC	089306092988

Product Literature and Photos

- [TAG1-100 \(Detailed Image\) \(gif\)](#)

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512