



TAG15-400

Dot Matrix Label, 1.0" X .50", 7 Across, Polyester, White, 5000/PK

Article Number: 595-15400

Part Number: TAG15-400

Type: TAG15

Base Data

Part No.	TAG15-400
Type	TAG15
Color	White (WH)
Features	• Tabtag Dot Matrix labels are specifically made for use in dot matrix printers for fast and easy printing. • Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.
Application Method	Labels are printed using a HellermannTyton thermal transfer printer and then applied by hand.

Product Dimensions

Length (L)	0.5" / 12.7mm
Width (W) (imperial)	1.0"
Width (W)	25.4mm
Height (H)	0.5" / 12.7mm
HR	27.94mm / 1.100"
Print Method	Dot-Matrix
Vertical Repeat	.667" / 16.94mm
Width of Liner (WL)	8.600" / 218.40mm

Material and Specifications

Material	Type 400, Polyester, white (WH)
Adhesive	Acrylic / Acryl
Adhesive Operating Temperature	-40 °F to +302 °F (-40 °C to +150 °C)
Curing Temperature	from +50 °F (from +10 °C)

Material Specification	RoHS
Operating Temperature	-40 °F to +302 °F (-40 °C to +150 °C)
ROHS Conformity Specification	 RoHS
Specification	UL-Recognized

Logistic and Packaging

Packaging Type	pack
Pkg. Qty.	5000 / 5000
Carton Qty.	5000Pieces
EAN code	4031026175270
Labels per Row	7
Minimum Order Quantity	5000
UPC	089306093466

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512