



## TAG77T1-101

Thermal Transfer Label, 3.0" X .937", 1 Across, Paper, White, 2000/RL

Article Number: 596-00020

Part Number: TAG77T1-101

Type: TAG77T1

### Base Data

---

<b>Part No.</b>	TAG77T1-101
<b>Type</b>	TAG77T1
<b>Color</b>	White (WH)
<b>Features</b>	<ul style="list-style-type: none"><li>• Thermal transfer labels are made with high performance materials for long term industrial applications.</li><li>• Labels can be printed in any standard thermal transfer printer giving the user options for printing and eliminating the need to be dedicated to one printer model.</li><li>• The labels are available in a wide variety of sizes so that finding a label for a particular application is easy.</li></ul>
<b>Application Method</b>	Labels are printed using a HellermannTyton thermal transfer printer and then applied by hand.
<b>Typical Application</b>	For Flat Surfaces Only

### Product Dimensions

---

<b>Width (W) (imperial)</b>	3.0"
<b>Width (W)</b>	76.2mm
<b>Height (H)</b>	0.9375" / 23.8mm
<b>HR</b>	76.2mm / 3.0"
<b>Print Method</b>	Thermal Transfer
<b>Vertical Repeat</b>	1.0" / 25.4mm
<b>Width of Liner (WL)</b>	3.12" / 79.2mm

### Material and Specifications

---

<b>Material</b>	Paper (PAP)
<b>Adhesive</b>	Acrylic / Acryl
<b>Adhesive Operating Temperature</b>	-65 °F to +200 °F (-54 °C to +93 °C)

**Operating Temperature** -65 °F to +200 °F (-54 °C to +93 °C)

**ROHS Conformity**  RoHS

### Logistic and Packaging

---

**Packaging Type** roll

**Pkg. Qty.** 2000 / 2000

**Labels per Row** 1

**Minimum Order Quantity** 2000

**UPC** 089306182092

### Product Literature and Photos

---

- [TAG77T1-101 \(Detailed Image\) \(gif\)](#)

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)

7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512