



Part Number [➔](#)

PKG.3B.025.CLLD12

Status Active

Size/Series 3B / B

Matching FGG.3B.025.CLAD12

[Request a quote](#)

MECHANICAL DETAILS

- Shell Style/Model** PK*: Fixed receptacle, nut fixing, cable collet
- Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
- Housing Material** Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
- Cable Fixing** D12: 10.8 - 11.9 mm **NEW COLLET**
- Variant** :

	A	B	E	L	M	S1	S2	S3	e
mm.	22	25	11.5	56	2	16.5	14	22	M18x1.0
in.	0.87	0.98	0.45	2.20	0.08	0.65	0.55	0.87	

PERFORMANCE DETAILS

- Insert Configuration** 3B.025 : 2 Fluidic, 10 Low Voltage
- Insulator** L: PEEK

OTHER CHARACTERISTICS

- Endurance (Shell)**
- Humidity (max):** <=95% [at 60 deg C /140 F]
- Vibration:** 15 g [10 Hz - 2000 Hz]
- Shock Resistance:** 100 g [6 ms]
- Salt Spray Corrosion:** >144 hr
- Climatical Category:** 50/175/21
- Shielding (min):** 75 dB (10 MHz)
- Shielding (min):** 40 dB (1 GHz)
- IP Rating** 50
- Catalog**

