	First Edition	Approved by	Production Div.
	May 12, 1999	Checked by	Quality Assurance Div.
LCD Module Specification	Final Revision		
***************************************	*****	Checked by	Design Engineering Div.
Type No. DMF – 5 0 8 4 0 N B – F W		Prepared by	Production Div.
Table of1. General Specifications2. Electrical Specifications3. Optical Specifications4. I/O Terminal5. Test6. Appearance Standards7. Code System of Production Lot8. Type Number9. Applying Precautions10. Precautions Relating Product Ha11. Warranty	ndling		3 8 10 12 13 16 16 16 17

Revision History

Rev.	Date		Page		Comn	nent		
DM	F-50840NB-FW	(AA) No	0.99-0101		EX CORPOR	RATION	Pac	ge 1/18

1. General Specifications

Operating Temp.	: min. 0°C \sim max. 50°C
Storage Temp.	: min20°C \sim max. 60°C
Dot Pixels	: 320 (W) \times 240 (H) dots
Dot Size	: 0.33 (W) \times 0.33 (H) mm
Dot Pitch	: 0.36 (W) \times 0.36 (H) mm
Viewing Area	: 120.0 (W) \times 90.0 (H) mm
Outline Dimensions	: 167.1 (W) × 109.0 ^{*1} (H) × 11.0 max. ^{*2} (D) mm *1 Without Connector *2 Without CFL Cable
Weight	: 230g max.
LCD Type	: NTD-15885 (STN / Blue-mode / Transmissive)
Viewing Angle	: 6:00
Data Transfer	: 4-bit parallel data transfer
Backlight	: Cold Cathode Fluorescent Lamp (CFL) $\times 1$
Drawings	: Dimensional Outline UE-36988

2. Electrical Specifications

2.1.Absolute Maximum Ratings

					Vss=0V
Parameter	Symbol	Conditions	Min.	Max.	Units
Supply Voltage	Vcc-Vss	_	-0.3	7.0	V
(Logic)					
Supply Voltage	V _{CC} -V _{EE}	_	0	35.0	V
(LCD Drive)					
Input Voltage	VI	_	-0.3	Vcc+0.3	V

2.2.DC Characteristics

Ta=25°C, Vss=0V

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Supply Voltage	Vcc-Vss	_	4.5	—	5.5	V
(Logic)						
	V _{CC} -V _{EE}	—	27.1	—	30.0	V
Supply Voltage						
(LCD Drive)	Vcc-Vadj		Shown in 3.	1		V
High Level	VIH	$V_{CC} = 5.0V \pm 10\%$	$0.8 \times V_{CC}$	—	Vcc	V
Input Voltage						
Low Level	VIL	$V_{CC} = 5.0V \pm 10\%$	0	—	$0.2 \times V_{CC}$	V
Input Voltage						
	Icc	V _{CC} -V _{SS} =5.0V	—	5.5	15.0	mA
Supply Current						
	IEE	V _{CC} -V _{ADJ} =23.3V	_	5.0	10.0	mA

2.3.AC Characteristics


$V_{CC}=5.0V\pm10$	0%
--------------------	----

Parameter	Symbol	Min.	Max.	Units
CP Frequency	\mathbf{f}_{CP}	—	6.0	MHz
Clock Pulse Width	twc	50	_	ns
Load Pulse Width	$t_{\rm WL}$	63	—	ns
Data Setup Time	t setup	30	—	ns
Data Hold Time	thold	30	_	ns
Clock Pulse Setup Time	$t_{\rm CL}$	80	_	ns
Clock Pulse Hold Time	t_{LC}	110	_	ns
Rise/Fall Time	tr, tf	—	Note 1	ns
FLM Setup Time	t_{FDS}	100	_	ns
FLM Hold Time	t _{FDH}	100	—	ns


Note 1: The rise and fall times (tr, tf) must satisfy the following relationships ((1) and (2)).


$$(1)$$
tr, tf< $\frac{1}{2f_{CP}}$ - t_{WC}


@tr, tf< 50 ns



This module contain these capacitors. Please be careful about timing characteristics.







2.7.Lighting Specifications


						Ta=	=25℃
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units	Notes
Lamp Voltage	VL	_	_	340	_	Vrms	1
Lamp Current	IL	_	3.0	4.0	5.0	mArms	2
Starting Voltage	Vs	_	850	_	_	Vrms	3
Surface Luminance	L	IL=4.0mA	_	60	_	cd/m^2	4
Average Life	Tal	IL=4.0mA	25000	_	_	hrs	5
Brightne Ratio	В	IL=4.0mA	70	_	_	%	


Note 1 : The voltage (r.m.s.) to maintain the electric discharge of the lamp. It is measured after lighting for 3 minutes.

Note 2 : The current (r.m.s.) to flow through the lamp with the electric discharge. It is measured after lighting for 3 minutes.

Note 3: The voltage at starting the electric discharge when the voltage is increased gradually from 0V.

- Note 4 : Surface Luminance is specified by the average of 9 luminance values measured at each point shown above after 20 minutes power on with the all ON pattern adjusted to maximum contrast and the dimming control of 100%. (maximum brightness)
- Note 5 : CFL life is defined as the time for which the initial luminance is attenuated by 50% of the luminance value. Average Life representes the time elapsed at the point of time when the residual ratio becomes below 50% when plural lamps are lighted in comparison with the definition of life mentioned above.





3. Optical Specifications

3.1.LCD Driving Voltage

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Recommended		Ta= 0°C	_	_	27.1	V
LCD Driving Voltage	Vcc-Vadj	Ta=25°C	21.7	23.3	24.9	V
Note 1		Ta=50°C	19.9	_	—	V

Note 1 : Voltage (Applied actual waveform to LCD Module) for the best contrast. The range of minimum and maximum shows tolerance of the operating voltage. The specified contrast ratio and response time are not guaranteed over the entire range.

3.2.Optical Characteristics

Ta=25°C, 1/240Duty, 1/14Bias, V_D=22.7V (Note 4), $\theta = 0^{\circ}$, $\phi = -^{\circ}$

Pa	rameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Contrast Rat	tio Note 1	CR	$\theta = 0^{\circ}, \phi = -^{\circ}$	_	5	—	
Viewing An	gle			Shown i	n 3.3		
Response	Rise Note 2	Ton	—	_	270	400	ms
Time	Decay Note 3	Toff	_	_	400	600	ms

Note 1 : Contrast ratio is definded as follows.

 $CR = L_{ON} / L_{OFF}$

LON: Luminance of the ON segments


LOFF : Luminance of the OFF segments


- Note 2 : The time that the luminance level reaches 90% of the saturation level from 0% when ON signal is applied.
- Note 3 : The time that the luminance level reaches 10% of the saturation level from 100% when OFF signal is applied.

Note 4 : Definition of Driving Voltage V_D

VD=VCC-VADJ-VBE

Assuming that the typical driving waveforms shown below are applied to the LCD Panel at 1/A Duty - 1/B Bias (A : Duty Number, B : Bias Number). Driving voltage V_D is definded as the voltage V_{0-P} when the contrast ratio (CR=L_{0N} / L_{0FF}) is at its maximum.





4.I/O Terminal

4.1.Pin Assignment


No.	Symbol	Level	Function	
1	D0	H/L	Display Data	
2	D1	H/L	Display Data	
3	D2	H/L	Display Data	
4	D3	H/L	Display Data	
5	DISPOFF	H/L	H : Display on L : Display off (Pull up Resister)	
6	FLM	H/L	First Line Marker	
7	NC	—	Non-connection	
8	LP	H→L	Data Latch Signal	
9	СР	H→L	Clock Signal for Shifting Data	
10	Vcc	—	Power Supply for Logic	
11	Vss		Power Supply (0V, GND)	
12	VEE		Power Supply for LCD Drive	
13	VADJ		Voltage Level for LCD Contrast Adjustment	
14	FG	—	Frame Ground	


<u>CN2</u>

No.	Symbol	Level	Function
5	CFL HOT	—	Power Supply for CFL (HOT)
6	NC	—	Non-connection
7	NC	—	Non-connection
8	CFL GND	_	Power Supply for CFL (GND)

4.2.Example of Power Supply

It is recommended to apply a potentiometer for the contrast adjust due to the tolerance of the driving voltage and its temperature dependence.





5.<u>Test</u>

No change on display and in operation under the following test condition.

No.	Parameter	Conditions	Notes
1	High Temperature Operating	$50^{\circ}\text{C} \pm 2^{\circ}\text{C}$, 96hrs (operation state)	
2	Low Temperature Operating	$0^{\circ}C \pm 2^{\circ}C$, 96hrs (operation state)	3
3	High Temperature Storage	$60^{\circ}\text{C}\pm2^{\circ}\text{C}$, 96hrs	4
4	Low Temperature Storage	-20°C±2°C, 96hrs	3, 4
5	Damp Proof Test	40°C±2°C, 90~95%RH, 96hrs	3, 4
6	Vibration Test	Total fixed amplitude : 1.5mm	5
		Vibration Frequency : $10 \sim 55$ Hz	
		One cycle 60 seconds to 3 directions of X, Y, Z for	
		each 15 minutes	
7	Shock Test	To be measured after dropping from 60cm high on	
		the concrete surface in packing state.	
		E G D C B A C C 60cm Concrete Surface E,F,G face : once	

Note 1 : Unless otherwise specified, tests will be conducted under the following condition. Temperature $\,:20\pm5^\circ\!C$

Humidity $:65\pm5\%$

Note 2 : Unless otherwise specified, tests will be not conducted under functioning state.

Note 3 : No dew condensation to be observed.

Note 4 : The function test shall be conducted after 4 hours storage at the normal temperature and humidity after removed from the test chamber.

Note 5 : Vibration test will be conducted to the product itself without putting it in a container.


6. Appearance Standards

6.1.Inspection conditions


The LCD shall be inspected under 40W white fluorescent light.

The distance between the eyes and the sample shall be more than 30cm.

All directions for inspecting the sample should be within 45 $^{\circ}$ against perpendicular line.



6.2. Definition of applicable Zones



A Zone : Active display area

B Zone : Area from outside of "A Zone" to validity viewing area


C Zone : Rest parts

A Zone + B Zone = Validity viewing area

6.3.Standards

No.	Parameter			Criteria			
1	Black and	(1) Round Shap	e				
	White Spots,		Zone	Acceptable Number			
	Foreign Substances	Dimension (n	Dimension (mm)		В	С	
]	$D \leq 0.1$	*	*	*	
		0.1 < 1	$D \leq 0.2$	3	5	*	
		0.2 < 1	$D \leq 0.25$	2	3	*	
		0.25< 1	D ≦0.3	0	1	*	
		0.3 < 1	D	0	0	*	
		D = (Long + Short) / 2 *: Disregard					
		(2) Line Shape	(2) Line Shape				
			Zone	Ac	ceptable Num	ber	
		X (mm)	Y (mm)	А	В	C	
			0.03≧W	*	*	*	
		2.0≧L	$0.05 \ge W$	3	3	*	
		1.0≧L	$0.1 \ge W$	3	3	*	
		_	- 0.1 <w< td=""><td colspan="3">In the same way (1)</td></w<>		In the same way (1)		
		X : Length					
		Total defects shall not exceed 5.					
2	Air Bubbles						
	(between glass		Zone		Acceptable Number		
	& polarizer)	Dimension (n	Dimension (mm)		В	С	
]	$D \leq 0.3$		*	*	
		0.3 < 1	$0.3 < D \leq 0.4$		*	*	
		0.4 < 1	$D \leq 0.6$	2	3	*	
		0.6 < 1	0.6 < D		0	*	
		* : Disregare	d				
		Total defects sh	all not exceed	3.			

No. Parameter		Criteria		
3	The Shape of Dot	(1) Dot Shape (with Dent) 0.15≧ As per the sketch of left hand.		
		(2) Dot Shape (with Projection)		
		Should not be connected to next dot.		
(3) Pin H		(3) Pin Hole		
		$(X+Y)/2 \leq 0.2 \text{ mm}$ (Less than 0.1 mm is no counted.)		
		(4) Deformation		
		Y (X+Y)/2≦0.2mm		
		X Total acceptable number : 1/dot, 5/cell		
		(Defect number of (4) : 1pc.)		
4	Polarizer Scratches	Not to be conspicuous defects.		
5	Polarizer Dirts	If the stains are removed easily from LCDP surface, the module is not		
		defective.		
6	Complex Foreign	Black spots, line shaped foreign substances or air bubbles between		
_	Substance Defects	glass & polarizer should be 5pcs maximum in total.		
7	Distance between	$D \leq 0.2$: 20mm or more		
	Different Foreign Substance Defects	$0.2 \le D: 40$ mm or more		
	Substance Defects	<u> </u>		



10. Precautions Relating Product Handling

The Following precautions will guide you in handling our product correctly.

- 1) Liquid crystal display devices
 - ① The liquid crystal display device panel used in the liquid crystal display module is made of plate glass. Avoid any strong mechanical shock. Should the glass break handle it with care.
 - ② The polarizer adhering to the surface of the LCD is made of a soft material. Guard against scratching it.

2) Care of the liquid crystal display module against static electricity discharge.

- ① When working with the module, be sure to ground your body and any electrical equipment you may be using. We strongly recommend the use of anti static mats (made of rubber), to protect work tables against the hazards of electrical shock.
- ② Avoid the use of work clothing made of synthetic fibers. We recommend cotton clothing or other conductivity-treated fibers.
- ③ Slowly and carefully remove the protective film from the LCD module, since this operation can generate static electricity.
- 3) When the LCD module alone must be stored for long periods of time:
 - ① Protect the modules from high temperature and humidity.
 - ② Keep the modules out of direct sunlight or direct exposure to ultraviolet rays.
 - ③ Protect the modules from excessive external forces.
- 4) Use the module with a power supply that is equipped with an overcurrent protector circuit, since the module is not provided with this protective feature.
- 5) Do not ingest the LCD fluid itself should it leak out of a damaged LCD module. Should hands or clothing come in contact with LCD fluid, wash immediately with soap.
- 6) Conductivity is not guaranteed for models that use metal holders where solder connections between the metal holder and the PCB are not used. Please contact us to discuss appropriate ways to assure conductivity.
- 7) For models which use CFL:
 - ① High voltage of 1000V or greater is applied to the CFL cable connector area. Care should be taken not to touch connection areas to avoid burns.
 - ② Protect CFL cables from rubbing against the unit and thus causing the wire jacket to become worn.
 - ③The use of CFLs for extended periods of time at low temperatures will significantly shorten their service life.

8) For models which use touch panels:

①Do not stack up modules since they can be damaged by components on neighboring modules. ②Do not place heavy objects on top of the product. This could cause glass breakage.

- 9) For models which use COG,TAB,or COF:
 - ①The mechanical strength of the product is low since the IC chip faces out unprotected from the rear. Be sure to protect the rear of the IC chip from external forces.
 - ②Given the fact that the rear of the IC chip is left exposed, in order to protect the unit from electrical damage, avoid installation configurations in which the rear of the IC chip runs the risk of making any electrical contact.
- 10) Models which use flexible cable, heat seal, or TAB:
- ①In order to maintain reliability, do not touch or hold by the connector area.
 ②Avoid any bending, pulling, or other excessive force, which can result in broken connections.

11.Warranty

This product has been manufactured to your company's specifications as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment, we cannot take responsibility if the product is used in medical devices, nuclear power control equipment, aerospace equipment, fire and security systems, or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required. If the product is to be used in any of the above applications, we will need to enter into a separate product liability agreement.

- ① We cannot accept responsibility for any defect, which may arise from additional manufacturing of the product (including disassembly and reassembly), after product delivery.
- ② We cannot accept responsibility for any defect, which may arise after the application of strong external force to the product.
- ③ We cannot accept responsibility for any defect, which may arise due to the application of static electricity after the product has passed your company's acceptance inspection procedures.
- ④ When the product is in CFL models, CFL service life and brightness will vary according to the performance of the inverter used, leaks, etc. We cannot accept responsibility for product performance, reliability, or defect, which may arise.
- (5) We cannot accept responsibility for industrial property, which may arise through the use of your product, with exception to those issues relating directly to the structure or method of manufacturing of our product.
- ⑥ Optrex will not be held responsible for any quality guarantee issue for defect products judged as Optrex-origin longer than 2 (two) years from Optrex production or 1(one) year from Optrex, Optrex America, Optrex Europe, Display LC delivery which ever comes later.