

PRODUCT NEWS

Product under development

Single 3W type

■Product outline

This is an LED module which uses high output 3W-type LED. It provides adequate light even with a single lamp, enabling it to be used for a variety of lighting applications.

■ Feature

- High color rendering: Ra96
- High luminous flux 90lm/3W at 5000K70lm/3W at 3300K
- Wide variations: Color Temp.: 5000K and 3300K, Lens: 25° or 45° in each color
- ●No soldering required, constant voltage and constant current circuit can be designed due to connected with socket board harness.

 (semi-custom made)



■Applications

● Spotlight ● Reading light, Picture light, Pendant light

[Product lineup]

Part number	LED color	Angle	Watts	CRI	Lumen	Dimensions
SIN3121N	White 5000K	25°	3W (21V-150mA)	Ra:96	90lm	Ф 34.8 × H20
SIN3141N		45°				
SIW3121N	Warm White 3300K	25°			70lm	
SIW3141N		45°				

[Applied products]









*The contents are current as of April 2007.

[Absolute maximum ratings]

Items	Absolute maximum ratings			
Forward current	150mA			
Reverse voltage	30V			
Operating Temp.	−30°C~+80°C			
Storage Temp.	−40°C ~ +85°C			



Attached Standard PCB dimensions



Dedicated socket with harness PC-board Constant voltage or constant current drive is possible as semi- custom design

Note: This product is not including heat-dissipation fins. You must use suitable heat-dissipation fins for this product.