

## PAC PAC-UNIV-HE10-LCF-5M

#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com



The pre-assembled PAC cable provide the electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following elements:

- PLC connection from the manufacturer.
- Multi-pole LIYY or LY YCY (shielded) cable with 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup> cross-section.
- SubD or RSV connectors for the connection to the interface.

The cables are automatically tested for continuity and isolation in order to guarantee their special functionality for which they were developed.

### **General ordering data**

Туре	PAC-UNIV-HE10-LCF-5M		
Order No.	<u>7789101050</u>		
Version	Pre-assembled cable, PAC, Cable LiYY, 0.14 mm <sup>2</sup>		
GTIN (EAN)	8430243959780		
Qty.	1 pc(s).		



# PAC PAC-UNIV-HE10-LCF-5M

### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany Fon: +49 5231 14-0

Fax: +49 5231 14-292083 www.weidmueller.com

### **Technical data**

Dimensions and weight	s		
Net weight	207.5 g		
Temperatures			
Operating temperature	-10+50°C	Storage temperature	-10+60 °C
General Data			
Connector PLC side	H0.14/10 (FERRULES 0.14mm²)	Interface connector	CONECTOR CABLE PLANO
Number of poles, min.	10-pole	Outer diameter	7 ± 1 mm
Cable	Cable LiYY	Cable length	5 m
Material	PVC	Wire cross-section	0.14 mm <sup>2</sup>
Electrical Data			
Rated voltage (text)		Permissible current strength per path,	
	≤ 60 Vdc ≤ 25 Vac	max.	1 A
Total current, max.	3 A	Resistance	≤ 150 mΩ/m
High voltage test	1 KV/1s		
Classifications			
eClass 6.2	27-24-92-05	eClass 7.1	27-14-11-52
Approvals			
Approvals	PG		
	ME25		
Downloads			
PDF	Colours chart		