

<p><b>Fig. 1</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 125V • Rated Current: 10A • Wire Size: 16-26AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Black</p>	<p><b>Fig. 2</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 15A • Wire Size: 12-28AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Gray</p>	<p><b>Fig. 3</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 15A • Wire Size: 12-28AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Gray</p>	
<p><b>Fig. 4</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 15A • Wire Size: 14-22AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Gray</p>	<p><b>Fig. 5</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 15A • Wire Size: 12-24AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Blue</p>	<p><b>Fig. 6</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 16A • Wire Size: 12-28AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Green</p>	
<p><b>Fig. 7</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 20A • Wire Size: 12-30AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Green</p>	<p><b>Fig. 8</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 15A • Wire Size: 12-24AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Black</p>	<p><b>Fig. 9</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 16A • Wire Size: 12-28AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Green</p>	
<p><b>Fig. 10</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 250V • Rated Current: 12A • Wire Size: 16-22AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Gray</p>		<p><b>Fig. 11</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 10A • Wire Size: 16-26AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Green</p>	
<p><b>Fig. 12</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 125V • Rated Current: 10A • Wire Size: 16-26AWG • Temp.: -40°C - 115°C • Flammability: UL 94V-0 • Color: Black</p>	<p><b>Fig. 13</b></p> <p><b>SPECIFICATIONS:</b> • Rated Voltage: 300V • Rated Current: 16A • Wire Size: 12-28AWG • Temp.: -30°C - 105°C • Flammability: UL 94V-0 • Color: Green</p>		

Fig.	No. of Pos.	Block Length (L) (mm)	Digi-Key Part No.	Price Each			On Shore Part No.	
				1	10	100		
<b>3.5mm Lead Spacing</b>								
1	2	7.00	ED2740-ND	.24	.22	.20	OSTTE020104	
	3	10.50	ED2741-ND	.36	.33	.30	OSTTE030104	
	4	14.00	ED2742-ND	.49	.44	.39	OSTTE040104	
	5	17.50	ED2743-ND	.61	.55	.49	OSTTE050104	
	6	21.00	ED2744-ND	.73	.66	.59	OSTTE060104	
	7	24.50	ED2745-ND	.85	.77	.69	OSTTE070104	
	8	28.00	ED2746-ND	.97	.88	.78	OSTTE080104	
	9	31.50	ED2747-ND	1.09	.99	.88	OSTTE090104	
	10	35.00	ED2735-ND	1.22	1.10	.98	OSTTE100104	
	11	38.50	ED2736-ND	1.34	1.21	1.07	OSTTE110104	
	12	42.00	ED2737-ND	1.46	1.32	1.17	OSTTE120104	
	14	49.00	ED2738-ND	1.70	1.54	1.37	OSTTE140104	
	16	56.00	ED2739-ND	1.94	1.75	1.56	OSTTE160104	
	<b>5.0mm Lead Spacing</b>							
	2	2	10.90	ED2714-ND	.46	.41	.37	OSTHG020080
		3	15.90	ED2715-ND	.67	.61	.54	OSTHG030080
4		20.90	ED2716-ND	.88	.80	.71	OSTHG040080	
5		25.90	ED2717-ND	1.10	.99	.88	OSTHG050080	
6		30.90	ED2718-ND	1.31	1.18	1.05	OSTHG060080	
7		35.90	ED2719-ND	1.52	1.38	1.22	OSTHG070080	
3	2	12.90	ED2722-ND	.68	.61	.55	OSTHT020080	
	3	17.90	ED2723-ND	.98	.89	.79	OSTHT030080	
	4	22.90	ED2724-ND	1.26	1.14	1.01	OSTHT040080	
	5	27.90	ED2725-ND	1.60	1.45	1.29	OSTHT050080	
	6	32.90	ED2726-ND	1.91	1.72	1.53	OSTHT060080	
	8	42.90	ED2727-ND	2.53	2.28	2.02	OSTHT080080	
	10	52.90	ED2721-ND	3.14	2.83	2.52	OSTHT100080	
	4	2	10.00	ED2705-ND	.50	.45	.40	OSTVA020180
		3	15.00	ED2706-ND	.75	.68	.60	OSTVA030180
		4	20.00	ED2707-ND	1.00	.90	.80	OSTVA040180
6		30.00	ED2708-ND	1.50	1.35	1.20	OSTVA060180	
8		40.00	ED2709-ND	2.00	1.80	1.60	OSTVA080180	

Fig.	No. of Pos.	Block Length (L) (mm)	Digi-Key Part No.	Price Each			On Shore Part No.	
				1	10	100		
5	2	10.00	ED2712-ND	.35	.32	.28	OSTTG020160B	
	3	15.00	ED2713-ND	.53	.48	.42	OSTTG030160B	
	6	2	10.00	ED2728-ND	.45	.41	.36	OSTVI020152
		3	15.00	ED2729-ND	.68	.61	.54	OSTVI030152
		2	10.00	ED2755-ND	.59	.53	.47	OSTVJ020152
	3	15.00	ED2756-ND	.88	.79	.71	OSTVJ030152	
<b>5.08mm Lead Spacing</b>								
8	2	10.16	ED2703-ND	.35	.32	.28	OSTTG025100B	
	3	15.24	ED2704-ND	.53	.48	.42	OSTTG035100B	
	9	2	10.16	ED2768-ND	.45	.41	.36	OSTVI022152
3		15.24	ED2769-ND	.68	.61	.54	OSTVI032152	
10	2	10.16	ED2770-ND	.61	.55	.49	OSTHD020080	
	3	15.24	ED2771-ND	.90	.82	.73	OSTHD030080	
	4	20.32	ED2772-ND	1.20	1.08	.96	OSTHD040080	
	5	25.40	ED2773-ND	1.49	1.35	1.20	OSTHD050080	
	11	2	10.16	ED2902-ND	.35	.32	.28	OSTYQ022150
3		15.24	ED2903-ND	.52	.47	.42	OSTYQ032150	
<b>7.0mm Lead Spacing</b>								
12	2	10.50	ED2748-ND	.25	.23	.20	OSTTE021104	
	3	17.50	ED2749-ND	.38	.34	.30	OSTTE031104	
	4	24.50	ED2750-ND	.50	.45	.40	OSTTE041104	
	5	31.50	ED2751-ND	.63	.57	.50	OSTTE051104	
	6	38.50	ED2752-ND	.75	.68	.60	OSTTE061104	
	7	45.50	ED2753-ND	.88	.79	.70	OSTTE071104	
	8	52.50	ED2754-ND	1.00	.90	.80	OSTTE081104	
	<b>7.50mm Lead Spacing</b>							
13	2	15.00	ED2730-ND	.48	.43	.39	OSTVI024152	
	3	22.50	ED2731-ND	.72	.65	.58	OSTVI034152	
	4	30.00	ED2732-ND	.95	.86	.77	OSTVI044152	
	5	37.50	ED2733-ND	1.19	1.08	.96	OSTVI054152	
	6	45.00	ED2734-ND	1.43	1.29	1.15	OSTVI064152	