





Rev	AWO #	Description	Date	Appr
-		RELEASED	8/25/14	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:

- Material: Insulator: PA66, rated UL 94V-0
- Insulator color: Green
- Screw: Steel, M3.0/Zinc plated
- Cage: Brass, Nickel plated
- Pin Header: Brass, Tin plated
- Electrical: Voltage rated: 300 VAC
- Current rated: 16 Amps
- Contact resistance: 20 mΩ
- Insulation resistance: 500 MΩ @ 500 VDC
- Withstanding voltage: 2000V AC/1 Min
- Mechanical: Solid wire: 26-12AWG 2.5mm²
- Torque (Lb-in): 0.5Nm (4.5lb-in)
- Temperature Rating: Operating temperature: -40°C to +105°C
- Environmental: Lead free, RoHS compliant.

Positions: 02 thru 24
 A = .197 [5.00] x No. of Positions
 B = .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: EURO BLOCK, .197 [5.00] PITCH

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN AY	8/25/14	X	EB147A-XX-C	-
CHECKED SC	8/25/14	X		
APPROVED				

REF: S00067C SCALE: NTS SHEET 1 OF 1

