

PLUG	RECEPTACLE	RECEPTACLE: MD 021 RS M2 45 XX XXX XX XX XX
<b>SERIES</b>		
MD .050" Rugged Metal Dust Cover	MD .050" Rugged Metal Dust Cover	
<b>SIZE</b>		
XXX 009, 015, 021, 025, 031, 037, 051, 069, 100	XXX 009, 015, 021, 025, 031, 037, 051, 069, 100	
<b>STYLE</b>		
RP Plug, rugged metal	RS Receptacle, rugged metal	
<b>PLATING</b>		
M2 Electroless nickel	M2 Electroless nickel	
M3 Electrodeposited cadmium <input checked="" type="checkbox"/>	M3 Electrodeposited cadmium <input checked="" type="checkbox"/>	
M4 Hard anodized black	M4 Hard anodized black	
<b>HARDWARE</b>		
STYLE OF HARDWARE:		
22 Two integrated jacks (62*)	22 Two integrated jacks (62*)	
45 Two turning jackscrews, allen head, captivated** (85*)	45 Two turning jackscrews, allen head, captivated** (85*)	

\* = Use number in parenthesis when ordering size 100.

\*\* = Captive hardware is factory installed and non-removable.

Not for use with rear panel mount connectors

Not for use on receptacles with grounding fingers

= Option not RoHS compliant