



PHYSICAL

Conductors: 24 AWG 19/34 Tinned Copper
 Insulation: .010" Nom. PVC
 Color Code: Brown, Red, Orange, Yellow, Green, Blue, Violet, Gray, White, Black and Repeat
 Temp. Rating: 105°C

ELECTRICAL

Voltage Rating: 300 V
 Current Rating: 2.2 A @ 10°C Rise Above Ambient
 Insulation Res.: 10¹⁰ ohms – 10 ft Min.
 Cable Style: UL AWM Style 2693 (105°C, 300V)

<u>Part Number</u>	<u>Count</u>	<u>Width, Nominal</u>	
111-2414-010	10	.45	(11,43mm)
111-2414-015	15	.675	(17,15mm)
111-2414-018	18	.81	(20,57mm)
111-2414-020	20	.90	(22,86mm)
111-2414-030	30	1.35	(34,29mm)
111-2414-032	32	1.44	(36,58mm)
111-2414-037	37	1.665	(42,29mm)

DRAWN	PROD ENG	QA	MKT	P/ECN#	DRAWING NO. 111-2414-0XX	AMPHENOL SPECTRA-STRIP 720 SHERMAN AVE TEL (203) 281-3200 HAMDEN CT 06514 FAX (203) 281-5872	Rev A
FITS 2/10/06	2/10/06			972	TITLE: Spectra-Bond® Parallel		SHEET 1 of 1
					Conductor Cable		