


NOTES:

- 1) LABEL REQUIREMENT:  
LABELS ARE M23053/5 ,WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
- 2) ASSEMBLY REQUIREMENT:
  - ASSEMBLY CAN BE BUILT AS SUB-ASSEMBLY PN 17053010D2-SUB USING ITEM 2, 3, 4, 5, 6.
  - DEPICTION OF ITEM 1, & 3 IS FOR REFERENCE ONLY.
- 3) TEST REQUIREMENT:
  - a. IL ≤ 1.0 dB @ 850 nm.
  - b. ENDFACE GEOMETRY:
    - PHYSICAL CONTACT PC: GR-326 BUT FIBER HEIGHT +/-50 nm
    - MT ENDFACE: EN-50377-15-1
  - c. ENDFACE VISUAL REQUIREMENT: PHYSICAL CONTACT PC: IEC-61300-3-35

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION			
REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



J1	PINOUT DIAGRAM	B LABEL INFORMATION
1		1
2		2
3		3
4		4
5		5
6		6
7		7
8		8
9		9
10		10
11		11
12		12

7	AFSI-PRE T BOX	BOX, SMALL FIBER CABLE 10X10X2 W/AFSI GRAPHICS	1
6	BSFT0600	FURCATION TUBE, 2MM ID600UM, BLACK	15.5 FEET
5	NFO1253M3-12	12 CHANNEL LITE FLIGHT	3.78 FEET
4	931-251-251	SIMPLEX LC CONNECTOR, MM, 2.0MM WHITE SHORT BOOT	12
3	CF-198137-000	FEMALE MT MOUNTING KIT	1
2	9734	KIT FERRULE 12F MM MT ELITE	1
1	CF-594011-01S	MT38999 WALL MOUNT RECEPTACLE, SHELL 11, SOCKET	1
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH

MATERIAL:		DfTR/Designer: <b>C. Hoang</b> 2017/10/20		
		Check By: <b>B. Waite</b> 2017/10/24		
		Manufacturing: <b>B. Waite</b> 2017/10/24		
		Market Manager/PLM: <b>Q. Abraham</b> 2017/10/25		
		Configuration Management: <b>L. Brown</b> 2017/11/13	TITLE: 12 CHANNEL MT38999 RECEPTACLE TO LC ASSEMBLY, MM	
DRILLED HOLE DIAMETER TOLERANCE		<small>DO NOT SCALE DRAWING UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL ON ANGLES ±3° 1 PL ±.1 2 PL ±.02 3 PL ±.010 INTERPRET DIM AND TOL PER ASME 14.5M-1994</small>		
NEXT ASSY		USED ON	SIZE <b>A</b>	CAGE CODE <b>0YPM2</b>
APPLICATION			DWG NO <b>17053010QA-D2</b>	REV <b>-</b>
			SCALE: NONE	SHEET 1 OF 1