



①	Length	Feet	mm	tolerance (mm)	③
001	1	305	+30.5/-15.3		
003	3	914	+45.8/-36.6		
005	5	1524	±45.8		
007	7	2134	±64.1		
010	10	3048	±91.5		
015	15	4572	±137.3		
020	20	6096	±183		
025	25	7620	±228.8		
050	50	15240	±457.5		
100	100	30480	±915		

SPECIFICATIONS:

- CONDUCTORS:
 - CONDUCTORS: 24AWG 7*0.19 ± 0.015mm
 - CONDUCTOR INSULATION COLOR CODING: ONE WHITE/ORANGE, ONE ORANGE, ONE WHITE/GREEN, ONE GREEN, ONE BLUE, ONE WHITE/BLUE, ONE WHITE/BROWN, ONE BROWN.
- CABLE JACKET
 - PRINTING ON THE JACKET: CM (UL) C(UL) 4P 24AWG UTP CAT.5E PATCH CABLE ISO/IEC 11801 & EN 50288 & ANSI/TIA-568-C.2
- CABLE ASSEMBLY
 - SEE SECTION A-A FOR DIMENSIONS
 - CABLE TIE: WHITE TIE
 - WIRING T568B COLOR
 - CONTACT PLUG: RJ45 8P8C 3u DC UL 94V-2
- CABLE JACKET COLOR: ACCORDING TO CUSTOMERS REQUEST
- Dielectric strength: 2.5KV dc-2seconds
- Working temperatures: -20~60° c

DK-1511-XXXXXX

color:
BL(black), WH(white), B(blue), G(grey)

Length: see table ①

ROHS compliant
Unit: mm

Scale	Free	Customer-No.	
TOLERANCE		Date	Name
X.	±X	24.06.2014	Joanna
X.X		20.09.2019	Amy
X.XX		06.04.2017	Amy
DIM	TOL	Approved	20.09.2019
X.°		07.12.2016	Amy
Angle	TOL	①	Update length version
		②	Add new length version
		③	Add tolerance for cable length
		④	Drawn
		⑤	Drawn
		⑥	Drawn
		⑦	Drawn
		⑧	Drawn
		⑨	Drawn
		⑩	Drawn



ASS 7160 CA

rev03

Replace

SHEET

1 2 3 4 5 6 7

A B C D E F G H