

NO.	PART NAME	MATERIAL	PLATING	REMARKS
1	HOUSING	POLYAMIDE		UL94V0
2	BOTTOM COVER	POLYAMIDE		UL94V0
3	RING TERMINAL	Cu-Ti	GOLD FLASH	25 MICRONS
4	SHUNT TERMINAL	BRASS	GOLD FLASH	30 MICRONS
5	TIP TERMINAL	BRASS	GOLD FLASH	30 MICRONS
6	SLEEVE (EARTH) TERMINAL	PBS	GOLD FLASH	30 MICRONS




9815 SW Allen, Suite 109  
 Beaverton, OR 97005  
 Phone: (503) 643-4899  
 800-275-4899  
 Fax: (503) 372-1286  
 Website: www.cui.com

**SPECIFICATIONS:**

1. RATED VOLTAGE-16 VDC
2. RATED CURRENT-300 mA
3. CONTACT RESISTANCE-100 MOHMS OR LESS UNDER ALL CONDITIONS, INCLUDING AFTER LIFE TESTING.
4. INSULATION RESISTANCE-100 MOHMS OR GREATER AT 500 VDC.
5. DIELECTRIC WITHSTAND VOLTAGE-500 VAC RMS FOR 1 MINUTE.

**SCHEMATIC**



PC FILE NAME: SJ-3515-SMT.DWG

COPYRIGHT 1999 BY CUI INC.

TITLE: <b>3.5mm SURFACE MOUNT AUDIO JACK-STEREO</b>		UNITS: Millimeters
PART NO. SJ-3515-SMT		
DRAWN BY: Todd R. White	APPROVED BY:	SCALE: 3X