


PART NO.:  
C71-1068-GYxx

LENGTH(FT):  
1, 2, 3 ...  
EXAMPLE: 1=1FT



X-XXXXX  
SERIAL No.:00001~99999  
LENGTH(FT):  
1, 2, 3 ...  
EXAMPLE: 1=1FT

WIRE CONNECTION

COLOR(568B)	P1	PAIRS	P2
WHITE/ORANGE	1	————	1
ORANGE	2	————	2
WHITE/GREEN	3	————	3
BLUE	4	————	4
WHITE/BLUE	5	————	5
GREEN	6	————	6
WHITE/BROWN	7	————	7
BROWN	8	————	8

**SPECIFICATION:**

- 1.CABLE: UTP CAT6A 28AWG\*4P(7/0.12), JACKET OUTER: PVC, OD: 3.8±0.20mm.
- 2.JACKET COLOR: GRAY
- 3.CONNECTOR: 8P8C PLUG, LONG BODY.
4. BOOT: Ø4.0mm, TRANSPARENT.
- 5.TESTING: 100% ELECTRICAL TESTING .

PART No.: C71-1068-GYxx  
PART NAME: w-Intense™, UTP CAT6A Slim 28AWG Patch Cord, Snagfree Boot with Labels, Gray, xxFT