#### Office

# JD-0700EU-2





Actual product may vary from the image shown

# Professional Wireless Desktop for Entry Level Users!

The compact and high-quality JD-0700EU-2 desktop set from CHERRY, features an excellent price/performance ratio, modern, flat design with gentle, quiet and durable wear-resistant keys.

### Facts & Features

- Whisper quiet keystroke keys with wear-resistant laser key legends
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- Symmetrical design: 3-Button mouse, suitable for both left-handed and right-handed operation
- Optical Sensor technology:1200 dpi
- Rapid installation: Simple plug and play
- Interference-free wireless connection: Maximum wireless range (up to 8 meters) using 2.4 GHz wireless technology
- Nano USB receiver

# Technical Data Housing and Key Color:

Black

# Weight (product):

Approx. 502 g/1.10 lbs (keyboard with battery), approx. 85 g/.18 lbs (mouse with battery), approx. 1.5 g/.003 lbs (receiver)

# Total Weight (with packaging):

Approx. 923 g/ 2.0 lbs



10m / 32.80'

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-20°C to 65°C / -4°F to 149°F

Operating Temperature:

0° C - 50° C / 32° F - 122° F

Current Consumption:

Typ. 3 mA (keyboard), Typ. 6 mA (mouse), max. 35 mA (receiver)

Interface:

**USB** 

Product approvals:

UL



c-tick



CE



FCC



TÜV/GS



### System Requirements:

USB connection

#### Delivery Volume:

- 1 battery (type AA)
- 1 nano USB transmission receiver
- Operating instructions in hard copy
- 1 battery (type AAA)
- 1 optical wireless mouse
- 1 wireless keyboard

## Dimensions (product):

458 x 170 x 20 mm / 18.03"x 6.69"x .78" (keyboard), 109 x 62 x 37mm / 4.2" x 2.4"x 1.4" (mouse), 18 x 13 x 5 mm / .70"x .51"x .19" (receiver)



#### Technical Data Cont.

## Packaging Dimensions:

Appprox. 549 x 200 x 45 mm / 23.6"x 8.2"x 2"

#### Reliability:

■ MTBF > 45,000 hours

#### Mouse:

Scanning: InfraredResolution: 1200 dpi

Number of Keys: 3

 Mouse Wheel Design: Scroll Wheel with Key

Function

Design: SymmetricalConnection: Wireless

Scanning Rate:Max. 2400/s

Housing Color: Black

Key Color: Black

# Keyboard:

Key Technology: LPK

Service Life, Standard Key: > 10 million

Key Operations

Inscription Layout: StandardNumber of Keys: 104 + 4

# Packaging Unit:

Number of products in the master package: 6 Number of master packages per pallet: 21

Warranty:

2 years

# Order Description

Order Number	Color	Number of Keys
JD-0700EU-2	Black	104+4 Keys

ZF Electronic Systems Pleasant Prairie, LLC 11200 88th Avenue Pleasant Prairie, WI 53158

USA

Phone: 262.942.6500

Internet: www.cherrycorp.com

Sales: 262.942.6500 E-Mail: cep\_sales@ZF.com Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.