

CS266-58-0-1A

Product SPEC.

Application area	2U and above 2U Server thermal solution.
Application for CPU Socket	LGA 1155/1156/1150
Application for CPU Type	Intel® Core™ i7-2600, i5-2500 series Intel® Core™ i3& i5,Xeon® Processor 3400 Series
Production technology	Aluminium base plate and Aluminium fin with 3pcs $\Phi 6$ "U" heatpipes plus DC fan.
Assembly Method	Screw plus spring.
Production dimension (mm)	88.0*89.0*65.0
Production weight (g)	318
Thermal interface material	AD66 (thermal conductivity>4.0)
Back bracket	Optional

Fan Spec.

Fan part number	FD6025U12D
Fan dimension (mm)	60L*60W*25H
Rated voltage (V)	12
Bearing type	Two ball
Speed (RPM)	5000
Maximum air flow (CFM)	40.4
Acoustic (dBA)	41
Lifetime (H)	70,000
Fan line	4pins with PWM function



