

DREMEL®



Multi-Max™ MM35-01 Tool Kit

Model # MM35-01

Product Specifications

The Dremel Multi-Max MM35 features 3.5 amps of power to easily tackle the toughest applications. The tool-less innovative design for quick and secure accessory change solves the pain point of needing a wrench to perform the same operation. The extra-wide 3.2-degree angle of oscillation delivers fast and precise cuts. The variable speed 10,000-21,000 OPM allows for optimal performance and control with a variety of materials. The provided soft bag is a great value added to store tool and accessories.

- Powerful: 3.5 Amp motor easily tackles the toughest applications
- Tool-less accessory change: innovative design for quick, secure accessory change without a wrench
- Fast and precise cuts: the extra-wide 3.2 degree oscillation angle provides the right speed to tackle any application
- Variable speed – from 10,000-21,000 OPM for optimal performance and control with a variety of materials
- Ergonomically optimized: soft grip for comfort and control
- 7 Ft. durable rubber cord: for a wide working range

DIMENSIONS	
Cord Length:	7[ft]
Case Type:	Bag
Tool Level:	1 - Corded – variable speed high
Warranty:	Limited 2 Years
Material:	Composite
Height:	3.5["]
Certifications:	CSA
Model Number:	MM35-01
Weight:	2.8[kg, lb, oz]
Amperage:	3.5
Voltage:	120V
Length:	14.2["]
Width:	2.5["]
Oscillating Angle:	3.2°