

## Energizer<sub>®</sub> TAC-R 700 NEW! Part Number ENPMTRL8

The Energizer® TAC-R 700 delivers high performance in a durable, dependable, and compact body. The rechargeable feature enables the user to charge the light using a USB cable. The rear push button, strobe mode, and durable aircraft grade aluminum were designed to work in various situations. In addition, the light output and four different modes (High, Medium, Low, Emergency Strobe), make it perfect for any outdoors and indoors usage, including work and DIY projects. Stay prepared in an emergency situation with this light's strike bezel head. Its removable clip works in both orientations which provides the versatility to clip and use whichever way works best for you.

## **Design Benefits**

- ✓ Rechargeable (USB Port)
- ✓ Durable aircraft grade aluminum
- ✓ Rear push button to easily change modes while holding the light
- ✓ Compact and lightweight
- ✓ Removable Clip
- ✓ Strike Bezel Head

## **Performance Benefits**

- ✓ MAXVIZ Technology to deliver a wide, powerful beam and high-definition vision
- ✓ Exceptional light output for any task
- ✓ Up to 15X Brighter than Standard LED Technology
- ✓ Emergency Strobe: ~17 Hz frequency

## **Light and Power Source**

- ✓ Features LED technology
- ✓ Rechargeable: Lithium Ion (18650) Non Removable battery















4 Operating Modes					
Mode	Lumens	Runtime	Beam Distance	Impact Resistant	Water Resistant
High	700	2hrs	100m	1m	IPX4
Medium	100	12hrs	-	1m	IPX4
Low	20	30hrs	-	1m	IPX4
Strobe	-	-	-	1m	IPX4