



LED DLC6SQ-2040e



Part #: EFDLC6DM/I/12W/1050/120D/50K/JB/E Fixture Class: 6" Slim Fixed

Product Description

LED DLC6SQ-2040e, delivering uniform brightness, this 6-inch LED downlight outputs 900 lumens in Bright White (4000K) color temperature. Designed with edge-lit LED technology and dimmable, this square downlight is the perfect solution for rooms where a recessed can or tall fixture won't fit. With spring action clips and a separate junction box, this LED downlight eliminates housing for quick and easy installation. See Euri Lighting DLC6SQ-2000e for welcoming Soft White (3000K) and DLC6SQ-2040e for vibrant Cool White (5000K).









Estimated Energy Cost: \$1.44 per year

*Note: Design, features and specifications subject to change without notice. Some features may not be available on all models. Please visit www.eurilighting.com or call 1-888-743-5766 for more information.

Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
12 W	120V/60Hz	900 lm	120°	NA cd	4000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base	Lamp Lifespan
80	75 lm/W	0.9	0.1 A	Junction Box	30,000 Hrs.

Product Features

Dimmable



Abutted & Covered




No Housing Required



Damp Rated

Product Dimensions



Product Photometric Data

