

Han 1A-3+PE-c-f shielded, latch



Image is for illustration purposes only. Please refer to product description.

Part number	09 10 003 3100
Specification	Han 1A-3+PE-c-f shielded, latch
HARTING eCatalogue	https://b2b.harting.com/09100033100

Identification

Category	Inserts
Series	Han [®] 1A

Version

Termination method	Crimp termination
Gender	Female
Locking type	Snap-in latches
Size	1 A
Shielding	With cable tie
Number of contacts	3
further contacts	+ shielding
PE contact	Yes
Details	Please order crimp contacts separately. Order separately the hoods/housings for an IP65 performance.

Details	<p>A Han[®] 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector. In this case protection against electric shock must be provided by the installation methods of the user.</p> <p>The Han[®] 1A insert has no conductive connection between PE-contact and shielding element. Protection against electric shock must be provided by connecting the cable shielding to a protective earth (PE). Contact inserts must not be coupled or decoupled under electrical load. Contact inserts must not be powered-up in the un-mated condition.</p>
Pack contents	Shielding element is included within the delivery

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
-------------------------	------------------------------



Technical characteristics

Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	$>10^8 \Omega$
Limiting temperature	-30 ... +90 °C
Mating cycles	≥ 100
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3 IEC 61373 Category 1 Class B EN 60664-1
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	15.6 g
Country of origin	Germany
European customs tariff number	85366990

Product data sheet
09 10 003 3100
Han 1A-3+PE-c-f shielded, latch

This product is not orderable anymore. Contact your local distribution partner for alternatives.



Pushing Performance

Commercial data

eCl@ss

27440205 Contact insert for industrial connectors