

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!



Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	12V DC
Rated Speed:	58 rpm
Rated Torque:	18 kg.cm
Termination Style:	Terminals

No-Load Speed:	74 rpm (+/- 10%)
No-Load Current:	<1 A
Stall Torque:	85 kg.cm
Max. Power:	16 W
Max. Effiicency:	36%





