



Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!



Specifications			
Gearhead Type:	Spur - Offset Shaft	No-Load Speed:	85 rpm (+/- 10%)
Motor Type:	Carbon - Brushed	No-Load Current:	< 0.35 A
Rated Voltage:	12V DC	Stall Torque:	108 kg.cm
Rated Speed:	76 rpm	Stall Current:	11.8 A
Rated Torque:	11 kg.cm	Max. Power:	23 W
Rated Current:	1.5 A	Termination Style:	Terminals

* Gearbox limitations are set at 25 kg.cm, operating past this torque limit may cause premature failure.

