

Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.





Specifications	
Gearhead Type:	Spur
Motor Type:	Carbon - Brushed
Rated Voltage:	12V DC
Rated Speed:	57 rpm
Rated Torque:	0.9 kg.cm
Rated Current:	150 mA

No-Load Speed:	75 rpm (+/- 10%)
No-Load Current:	< 50 mA
Stall Torque:	3.82 kg.cm
Max. Power:	0.74 W
Max. Effiicency:	27%
Termination Style:	Terminals





