



SS Stainless Steel

4 Type

- A** Without bores (Only stainless steel)
- B** With through holes
- C** With countersunk holes

Metric table

2

Dimensions in: millimeters - inches

l_1	l_2		d_1	d_2	d_3	d_4	m_1	m_2	m_3	s
30	Square	1.5x elongated	3	3.2	4	6.4	18	18	16.5	1.5
1.18	1.18	1.77	0.12	0.13	0.16	0.25	0.71	0.71	0.65	0.06
40	40	60	4	4.2	5	8.3	25	25	22.5	2
1.57	1.57	2.36	0.16	0.17	0.20	0.33	0.98	0.98	0.89	0.08
50	50	75	6	5.2	5	8.3	30	30	27.5	2
1.97	1.97	2.95	0.24	0.20	0.20	0.33	1.18	1.18	1.08	0.08
60	60	90	6	5.2	5	8.3	36	36	33	2
2.36	2.36	3.54	0.24	0.20	0.20	0.33	1.42	1.42	1.30	0.08

Specification

1

Body

- Steel, zinc plated, blue passivated finish **ST** (Only Type B and C)
- Stainless steel **NI** European Standard No. 1.4301 (AISI 304)

- Pin Stainless steel European Standard No. 1.4301 (AISI 304) Riveted

• RoHS compliant

Information

GN 136 sheet metal hinges are a low-cost option for light load applications.

Type A can be fixed in place by welding or by using holes made by the customer.

see also...

- List of Hinge Types
- Sheet Metal Hinges GN 1362
- Sheet Metal Hinges GN 1364
- Hinges GN 1366

How to order

GN 136-NI-40-40-A

- 1** Material
- 2** Width l_1
- 3** Length l_2
- 4** Type