



Inch table



Dimensions in: inches - millimeters

d ₁ Thread	d ₂	d ₃	d ₄	h	k	Length l	Load bearing capacity
3/8 x 16	0.88 22.4	2.00 50.8	1.25 31.8	2.50 63.5	0.38 9.7	0.63 16.0	2700 lbf 12010 N
1/2 x 13	0.88 22.4	2.00 50.8	1.25 31.8	2.50 63.5	0.38 9.7	0.63 16.0	2700 lbf 12010 N
5/8 x 11	1.38 35.1	2.50 63.5	1.50 38.1	3.00 76.2	0.50 12.7	0.75 19.1	5000 lbf 22241 N
3/4 x 10	1.38 35.1	2.50 63.5	1.50 38.1	3.00 76.2	0.50 12.7	0.75 19.1	5000 lbf 22241 N
7/8 x 9	2.03 51.6	3.38 85.9	1.63 41.4	3.97 100.8	0.88 22.4	1.34 34.0	10000 lbf 44482 N
1 x 8	2.28 57.9	3.75 95.3	1.75 44.5	4.84 122.9	1.03 26.2	1.69 42.9	10000 lbf 44482 N

Specification

- Carbon steel 1030
- Forged
- Zinc plated



ST

Information

WN 583 lifting eye nuts offer a high load bearing capacity and are tested to meet high safety standards.

see also...

- *Lifting Eye Bolts WN 580*
- *Lifting Eye Nuts DIN 582 (Metric Size)*
- *Safety Swivel Lifting Eye Nuts GN 583 (Metric Size)*

<p>How to order</p> <p>WN 583-1X8-ST</p>	1	Thread d ₁
	2	Material