

## Technical data sheet

### Connection cable

Part no.: 50140222

KD U-M83W-V2110-100

#### Contents

- Technical data
- Electrical connection
- Circuit diagrams




Figure can vary



## Technical data

### Electrical data

#### Performance data

Operating voltage	Max. 60 V AC/DC
-------------------	-----------------

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M8
Type	Female
Handle body material	TPU
No. of pins	3 -pin
Version	Angled
Lock	Screw fitting, nickel-plated brass, recommended torque 0.5 Nm, self-locking

#### Connection 2

Type of connection	Open end
--------------------	----------

#### Cable properties

Number of conductors	3 Piece(s)
Wire cross section	0.34 mm <sup>2</sup>
AWG	22
Sheathing color	Yellow
Shielded	No
Silicone-free	Yes
Cable design	Connection cable (open on one end)
Cable length	10,000 mm
Sheathing material	TPE
Wire insulation	SR-PVC
Suitability for drag chains	No

### Mechanical data

Width across flats	9.6 mm
Bending cycles	1,000,000 Piece(s)

### Operation and display

### Environmental data

Ambient temperature, operation, flexible use	-10 ... 80 °C
Ambient temperature, operation, stationary use	-30 ... 80 °C

### Certifications

Degree of protection	IP 65
	IP 67
	NEMA 6P

### Classification

Customs tariff number	85444290
eCl@ss 5.1.4	27279201
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
eCl@ss 10.0	27060311
eCl@ss 11.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855

## Electrical connection

### Connection 1

Type of connection	Connector
Thread size	M8
Type	Female
Handle body material	TPU
No. of pins	3 -pin
Version	Angled
Lock	Screw fitting, nickel-plated brass, recommended torque 0.5 Nm, self-locking

### Connection 2

Type of connection	Open end
--------------------	----------

## Circuit diagrams

### Wiring schematic

