

Lilliput TK1500-NP/C/T - 15" HDMI touchscreen open frame monitor

Screen Size (diagonal)	15 inches
Aspect Ratio	4:3
Native Resolution	1024x768
Scan Frequency (Hz)	60-72
Viewing Angle (degrees)	170 / 170
Brightness Ratio (cd/m2)	300
Contrast Ratio	1500:1
Backlight	LED
Video Inputs	HDMI, DVI, VGA, composite (BNC)
Touchscreen Technology	5 wire resistive
Input Power	12V
Mounting Options	VESA 75, VESA 100
Contents Of Box	
Product	1 x TK1500-NP/C/T
Connection Cables	1x HDMI cable, 1 x VGA Cable, USB A-A Cable,
Power Adaptor	12V DC (UK, EU and US available)

Dimensions	
Height (mm)	402
Width (mm)	289
Depth (mm)	45.5
Weight (g)	3500
Environment	
Operating Temperature	-20°C ~ 60°C
Storage Temperature	-30°C ~ 70°C