

- Advanced AFE with High Accuracy and Temperature Stability
- Four Independent ADCs Measuring Four Current Channels and Three Voltage Channels
- 0.1% Wh Accuracy over 2000:1 Current Range
- Digital Temperature Compensation for Metrology and RTC
- 40Hz–70Hz Line Frequency Range, Phase Compensation ($\pm 10^\circ$)
- Low-Power 5ksps Auxiliary ADC for Environmental Monitoring
- On-Chip Digital Temperature Sensor
- Highly Integrated Product Features and Flexible Peripherals Support Broad Application Needs
 - LCD Controller Supporting Up to Eight Common Planes
 - Two PWM Control Channels with Programmable Frequency, Duty Cycle, Ramp Time
 - Two Touch Switch Inputs
 - Oscillator Based on 32kHz Watch Crystal with Internal 24MHz Backup R/C Oscillator
 - SPI (Master and Slave), Master I²C

- Four UARTs (Configurable Pins), Smart Card Interface, 38kHz IR Decoder
- 100-Pin LQFP