

100ft CAT 6A Ultra Slim Patch Cable (Blue) E09-100BL-SLIM



- ULTRA SLIM CABLE OD=4.6mm, High Performance Cat6a, 28 AWG, UL Listed, RJ45 Ethernet Cable Very convenient for traveling.
- Upload & Download Speed Support Bandwidth Up To 500MHz & Transmitting data at speeds of up to 10Gbps ,Connect To LAN/WAN Segments And ● Networking Gear At Maximum Speeds.
- Provides universal connectivity for LAN network components such as PCs, computer servers, printers, routers, switch boxes, network media players, NAS, VoIP phones, PoE devices, and more.
- The extra performance is ideal for Power over Ethernet (PoE) and Voice Over Internet Protocol (VoIP) applications where data loss is audibly and visually seen and heard.
- Snagless molded design provides strain relief & protection while maximizing on bending radius.
- 28AWG pure copper conductors 50u" gold plated contacts.

Features:

- Less Space
- Improved Airflow
- Improved Cooling
- Lower Operating Costs
- Tangle Free Latch
- Available Lengths: 100, 50, 25, 14, 7, 3, 1 ft