

100ft CAT 6A Industrial Outdoor-Rated Shielded Ethernet Cable, White (E09-100W-OUT)



This Micro Connectors industrial outdoor-rated CAT 6A shielded cable is perfect for your indoor office or outdoor house cabling project. This quality cable is made to withstand rugged outdoor environment providing UV and water resistant along with shielding to maximize performance by minimizing EMI/RFI and eliminating crosstalk. It comes with metal shielded RJ45 connector assembled and made with pure bare copper conductors for better conductivity and supports Power over Ethernet devices.

- UV and water resistant designed to withstand sunlight, dirt, and moisture.
- Metal shielded RJ45 connectors installed with strain relief for convenience
- U/FTP Unshielded Foiled Twisted Pair
- Ideal for data, voice and security applications requiring outdoor placement
- Supports Power over Ethernet: PoE, PoE+, and PoE++
- Meets ANSI/TIA-568-C specifications and UL, RoHS

Connector Metal Shielded RJ45 **Conductor** Solid Bare Copper

Shielding Unshielded Foiled Twisted Pair (U/FTP)

Wire Gauge 26 AWG
Outer 6.0 mm

without us, you are just not connected!

Micro Connectors, Inc. Hayward, CA 94545 Tel: 510.266.0299 Fax: 510.266.0289 www.MicroConnectors.com

MICRO CONNECTORS®

Dimensions

Certifications Meets ANSI/TIA-568-C specifications

and UL

RoHS and REACH compliant