

The Woodhead Express program provides a short list of industry standard products that can also be found in our Woodhead Electrical catalog. Woodhead Express parts average an actual leadtime of 2 days or less.

#### **ELECTRIC REELS**

Product Type	Wire Gauge / Conductor	Cord Type	Primary Cord Length (inches)	Secondary Cord End	Secondary Cord Length (feet)	Current Rating (A)	Retraction Weight (lb)	Woodhead No.	Order No.	
	16 AWG / 3				35.0	6.0	2	945-3	130090-0009	
	14 AWG / 3			Flying Leads	45.0	11.0		990WC	130090-0117	
								980	130091-0013	
	16 AWG / 3			Pendent box with 2 NEMA 5-15 duplex receptacles	50.0	8.0		980-3000	130091-0023	
				Flying leads				990	130091-0045	
Cord reel	14 AWG / 3	SJTOW	18.0	Pendent box with 2 NEMA 5-15 duplex receptacles	45.0	11.0	3	990-3000	130091-0057	
				Flying leads				997	130091-0085	
				Pendent box with 2 NEMA 5-15 duplex receptacles	35.0	15.0		997-3000	130091-0090	
	12 AWG / 3	12 AWG / 3			GFCI Pendant Oultet Box, One Duplex, NEMA 5-15 Outlet				997-3070G	130091-0094
		SOOW N/A	N/A	Flying Leads	50.0	18.0	4	435D	130083-0210	
12 AWG / 3	12 AWG / 3				50.0	18.0		92433	130083-0232	
	10 AWG / 3		Flying Leads	40.0	22.0		92434	130083-0233		
	14 AWG / 3			Trying Leads	50.0	14.0		9358	130083-0249	
	12 AWG / 3	2 AWG / 3						9383	130083-0264	
			N/A	Super-Safeway <sup>™</sup> NEMA 5-20 connector	25.0	18.0 4		9383-1533	130083-0265	
Cable reel				Rubber pendent box with (2) NEMA 5-20 duplex receptacle			4	9383-3080	130083-0271	
				Flying Leads	35.0			9385	130083-0279	
				Rubber pendent box with (2) NEMA 5-20 duplex receptacle	50.0			92433-3080	130083-0787	
	10 AWG / 3			Flying leads	20.0	22.0		9242	130084-0318	
	10 AWG / 4			Flying Leads	50.0	20		92544AN	130084-0141	
Static	2 (2 2 )	Galvanized			25.0			143025	130177-0003	
discharge	3/32"	steel cable	N/A	100.0A ground clamp	50.0	N/A	N/A	143050	130177-0005	
Head 2.1		Cable not	NI/A	#16/3 - 200.0' #14/3 -	125.0' #12/3 - 100.0	' (SOOW)	A1/A	HW100	130087-0071	
Hand wind	Cable not sussilied	supplied	N/A	Same as HW100	Same as HW100	N/A	N/A	930	130087-0057	
Ground	Cable not supplied	NI/A	NI/A	NI/A	N1/A	N1/A	N1/A	GR1000L	130084-0077	
Fault Reel			N/A	N/A	N/A	N/A	N/A	N/A	GR900	130083-0154

## **HOSE REELS**

Product Type	Inlet Hose Fitting (NPT)	Hose Inner Diameter	Length (feet/m)	Pressure (psi)	Old Order No.	Order No.
VDD been week	3/8"	2 (0)	30 / 0 1		DA330	130161-0007
VPR hose reel		3/8"	30 / 9.1	300.0	DB350	130161-0009
Premium hose reel	1/2"	1/2" 50 / 15.24			PBL450	130158-0038



# **TOOL SUPPORT**

Product Type	Construction	Weight Range (lb/kg)	Travel (feet)	Woodhead No.	Order No.
Positioner		1.0 - 10.0 / 0.5 - 4.5	4.7	GM31	130169-0002
	-	0.0 - 2.0 / 0.0 - 0.9	6.6	RB2	130173-0036
		1.0 - 2.0 / 0.5 - 0.9	10.0	RB210	130173-0037
				RB4	130173-0048
	Plastic Housings	2.0 - 4.0 / 0.9 - 1.8		RB4SC	130173-0050
		4.0 - 6.0 / 1.8 - 2.7	6.6	RF6	130173-0055
		6.0 - 8.0 / 2.7 - 3.6	6.6	RF8	130173-0061
		4.0 - 6.0 / 1.8 - 2.7		RFL6	130173-0069
		6.0 - 8.0 / 2.7 - 3.6		RFL8	130173-0074
Retractor		10 50/04 22		5F	130175-0014
		1.0 - 5.0 / 0.4 - 2.3		5FLR	130175-0016
	Sheet Metal Housings	40 100/10 45		10F	130175-0001
		4.0 - 10.0 / 1.8 - 4.5		10FLR	130175-0003
		0.0 15.0 (2.6 6.0	8.0	15F	130175-0006
		8.0 - 15.0 / 3.6 - 6.8		15FLR	130175-0008
	Casted Aluminum	4.0 - 10.0 / 1.8 - 4.5		10FLRC	130174-0001
	Housings	8.0 - 15.0 / 3.6 - 6.8		15FLRC	130174-0005
		16.0 - 22.0 / 7.3 - 10.0		22FLRC	130174-0009
		4.0 - 8.0 / 1.8 - 3.6		AB8	130237-0002
			4.0	AB8RL	130237-0005
		0.0 11.0 / 2.6 5.0	4.9	AB11	130237-0003
		8.0 - 11.0 / 3.6 - 5.0		AB11RL	130237-0006
		9.0 - 13.0 / 4.1 - 5.9		BF13	130170-0015
	Plastic Housings	13.0 - 18.0 / 5.9 - 8.2		BF17	130170-0017
		3.0 - 6.0 / 1.4 - 2.7		BF6	130170-0021
		6.0 - 9.0 / 2.7 - 4.1	6.6	BF9	130170-0023
		13.0 - 18.0 / 5.9 - 8.2		BFL18	130170-0027
		18.0 - 24.0 / 8.2 - 10.9		BFL24	130170-0030
Balancer		6.0 - 9.0 / 2.7 - 4.1		BFL9	130170-0033
		18.0 - 25.0 / 8.2 - 11.4		25EB	130171-0300
		25.0. 25.0./11.4. 15.0		35EB	130171-0302
		25.0 - 35.0 / 11.4 - 15.9		35EBR	130171-0303
		25.0 45.0 / 15.0 20.5		45EB	130171-0305
		35.0 - 45.0 / 15.9 - 20.5		45EBR	130171-0306
	Casted Aluminum	45.0 - 60.0 / 20.5 - 27.3	4.9	65EBS	130171-0309
	Housings	84.0 - 115.0 - 38.0 - 52.0	7.0	110KA	130172-0026
		29.0 - 40.0 / 13.0 - 18.0	6.0	40EA	130172-0184
		40.0 - 55.0 / 53.0 - 70.0		50JA	130172-0199
		53.0 - 70.0 / 24.0 - 32.0	7.0	70JA	130172-0221
		68.0 - 86.0 / 31.0 - 39.0		80JA	130172-0241
Static discharge reel		N/A	50.0	2050	130177-0009
Torque real	Sheet Metal Housings	0.0-15.0	15.0	1515T	130176-0004
Torque reel		15.0 / 6.8	15.0	1515TR	130176-0009
Replacement Part	N/A	N/A	N/A	31184-80	130179-0603
	Assy Drum	and Pin For 7' Cable For J/K I	Balancers	31091-1	130179-0610
Hose/cable hanger	Light duty composite	12.50 to 23.00mm (0.49 to 0.91")	N/A	61020	130179-0962



#### **SAFEWAY® PLUGS AND CONNECTORS**

Connector/Plug/Adapter	Configuration	Poles/Wires	Voltage	Description	Woodhead No.	Order No.
Connector	NEMA 5-20		125V	High impact	5269	130144-0044
Plug	NEMA 5-15		125V	підії іпірасс	5266	130144-0036
	NEMA L5-15	2-pole, 3-wire	125V	Non-NEMA15A- 125V Plug to NEMA 5-15R	1704	130151-0013
	NEMA L5-20			L5-15P to 5-15R	1705	130151-0014
Adapter	NEMA 5-20			5-15P to L5-15R	1712	130151-0017
Adapter	NEMA 5-15			Red Husk 20A125/ 250V Plug to NEMA 5-20R	1730	130151-0020
	NEMA L5-15			L5-20P to 5-20R	1740	130151-0023
	NEMA L5-20			Red Husk 5-15P to L5-20R	1744	130151-0025

## **SUPER-SAFEWAY™ PLUGS AND CONNECTORS**

Connector/Plug/Cordset	Poles/Wires	Configuration	Voltage	Current	Woodhead No.	Order No.
		NEMA 5-20		20.0A	1533	130141-0025
	2-pole, 3-wire	NEMA 5-15			1547	130141-0031
		NEMA L5-15	125V	15.0A	2547	130141-0056
Connector	3-pole, 3-wire	Non-NEMA locking			2507	130141-0053
	2-pole, 3-wire NEMA L5-20			20.0A	2747	130142-0021
	3-pole, 3-wire	Non-NEMA	250V	30.0A	2908	130145-0066
	2-pole, 3-wire	NEMA 5-20		20.0A	1433	130141-0010
	z-poie, s-wire	NEMA 5-15		15.0A	1447	130141-0015
Dlug	3-pole, 3-wire	Non-NEMA locking	125V		2407	130141-0044
Plug	2 1 - 2	NEMA L5-15			2447	130141-0047
	2-pole, 3-wire	NEMA L5-20		20.0A	2647	130141-0062
	3-pole, 3-wire	Non-NEMA	250V	30.0A	2808	130142-0031
Cordset, 50 feet 14/3 SOOW Cable	2-pole, 3-wire	NEMA 5-15	125V	15.0A	1447B143	130143-0102

#### **FESTOON**

Туре	Description Length		Travel Speed - Maximum	Wire/Cable Type	Woodhead No.	Order No.
Box Track	5400 Track 12 ft Section 12GA	0.30M (11.81")	53.34 MPM (175 FPM)	N/A	540012	130118-0007



### **WATERTITE® CONNECTORS AND PLUGS**

Description	Poles/Wires	Configuration	Voltage	Woodhead No.	Order No.
		NEMA L6-30	250V	28W48	130147-0074
		NEMA L5-15	105)/	24W47	130146-0082
D.		NEMA L5-20	125V	26W47	130147-0018
Plug		NEMA L7-15	277V	24W34	130146-0079
		NEMA 5-15		14W47	130146-0031
	2-pole, 3-wire	NEMA 5-20	125V	14W33	130146-0022
Plug (black)		NEMA 5-15		14W47BLK	130146-0032
		NEMA 6-15	250V	14W49	130146-0044
		NEMA 5-15	125V	59W47	130146-0116
		NEMA L6-20	250V	26W48	130147-0021
Plug		NEMA L5-30	1251/	28W47	130147-0072
	2 1 2 1 15 04	Non-NEMA	125V	14W07	130146-0015
	3-pole, 3-wire,15.0A	Non-NEMA		24W07	130146-0078
		NEMA L14-20	250V	26W74	13014-70025
		NEMA L15-20		26W75	130147-0027
		NEMA L16-20	480V	26W76	130147-0029
	3-pole, 4-wire	NEMA L14-30		28W74	130147-0077
		NEMA L15-30	250V	28W75	130147-0079
		NEMA L16-30	480V	28W76	130147-0081
	4-pole, 4-wire	4-pole, 4-wire Non-NEMA		26W09	130147-0015
	4-pole, 5-wire	NEMA L21-20	208V	26W81	130147-0031
	4-pole, 5-wire	NEMA L21-30		28W81	130147-0085
Connector (black)		NEMA 5-15	125V	15W47BLK	130146-0061
		NEMA 5-20		15W33	130146-0052
		NEMA 5-15	125V	15W47	130146-0060
		NEMA L7-15	277V	25W34	130146-0095
		NEMA L5-15		25W47	130146-0099
		NEMA L5-20	125V	27W47	130147-0044
	2-pole, 3 wire	NEMA L6-20	250V	27W48	130147-0048
		NEMA L5-30	125V	29W47	130147-0093
		NEMA L6-30	250V	29W48	130147-0096
		Non-NEMA	125V	15W07	130146-0050
		Non-NEMA		25W07	130146-0092
Connector		Non-NEMA		27W08	130147-0035
		NEMA L14-20	250V	27W74	130147-0053
		NEMA L15-20		27W75	130147-0056
		NEMA L16-20	480V	27W76	130147-0059
	3-pole, 4-wire	NEMA L14-30		29W74	130147-0102
		NEMA L15-30	250V	29W75	130147-0105
		NEMA L16-30	480V	29W76	130147-0108
		NEMA L17-30	600V	29W77	130147-0111
	4-pole, 4-wire	Non-NEMA	208V	27W09	130147-0038
	4-pole, 5-wire	NEMA L22-30	480V	29W82	130147-0118
Duplex flip lid with female 5-15 receptacle	-	NEMA 5-15		60W47DPLX	130146-0131
Duplex flip lid with female 5-20 receptacle		NEMA 5-20	1	60W33DPLX	130146-0125
·	2-pole, 3-wire	NEMA 5-20	125V	60W33	130146-0123
Receptacle with single flip coverplate		NEMA 5-15	-	60W47	130146-0129
Receptacle with single flip coverplate with locking blade		NEMA 5-15	-	65W47	130146-0149



### **PORTABLE OUTLET BOXES**

Configuration	Description	Woodhead No.	Order No.
Multiple outlet box, shell only	Standard depth two duplex outlet box with coverplate only	3000	130137-0087
Multiple outlet box, shell only	Standard depth outlet box with MAX-LOC® cordgrip (F2)	3059	130137-0149
Multiple outlet box, shell only	Standard depth outlet box with MAX-LOC® cordgrip (F3)	3099	130137-0216
NEMA 5-15R	Standard depth outlet box with(2) duplex	3000-1	130137-0088
Multiple outlet box, shell only	Standard depth outlet box with clamping cordgrip	3050	130137-0147
NEMA 5-20	Deep box with (2) NEMA 5-20 duplex	3085-10	130137-0192
Duplex cover plate with flip lids for portable outlet box	Duplex cover plate with flip lids for portable outlet box	3056	130138-0025
Duplex cover plate for portable outlet box	Duplex cover plate for portable outlet box	3051	130138-0020
Blank cover plate for portable outlet box	Blank cover plate for portable outlet box	3054	130138-0023
3 NEMA 5-15 outlets	Multi-tap outlet box	31593	130136-0033
NEMA 5-20	Multi-Tap Strip (3) Outlet Box with Buss Bars	31565	130136-0025

### **PUSHBUTTON/TEST INSTRUMENTS**

Description	Woodhead No.	Order No.
Plastic two-button pendant	4052	130126-0231
Two-button station	4022	130126-0199

### **GFCI**

Configuration	Current	Manual/ Automatic	Description	Woodhead No.	Order No.
			Super-Safeway GFCI with flying leads, 2' cord	20051-0M	130153-0110
NEMA 5-20	20.04		Super-Safeway GFCI, 2' cord, Watertite® plug and connector	20052-1M	130153-0126
	20.0A		Safeway GFCI, Manual in-line, plug and connector	20051-1	130153-0111
			Safeway GFCI, In-line field attachable	20054	130153-0144
		Manage	Safeway GFCI, In-line, molded plug and connector	15050-1	130153-0019
		Manual	Safeway GFCI, field attachable right angle plug only	15054	130153-0089
NIEMA E 1E	15.04		Safeway GFCI, Molded plug and tri-tap connector	15050-3TT	130153-0028
NEMA 5-15	15.0A		In-line Safeway <sup>™</sup> right angle plug, connector, 2' cord	15054-1	130153-0090
			Safeway In-Line Manual Reset Molded plug and tri-cord	15050-50TT	130153-0033
			Super-Safeway In-Line Industrial Manual Reset Molded	15050-1M	130153-0021



### **CABLE GRIPS**

Grip Type	Orientation	Cable Diameter Range	Connection Type	Woodhead No.	Order No.
		.375500"		36254	130097-0163
		.500625"	1/2" NPT Male	36256	130097-0165
Deluxe cord	Straight	.500625"		36261	130097-0168
		.625750"	3/4" NPT Male	36263	130097-0170
		.875-1.000"	1" NPT Male	36269	130097-0173
		.300430"		36503	130097-0258
		.400540"	1/2" NPT Male	36505	130097-0260
Wide-range	Straight, insulated bushing	.520730"	3/4" NPT Male	36508	130097-0262
	, , , , , , , , , , , , , , , , , , , ,	.700970"	1" NPT Male	36512	130097-0265
		.940-1.250"	1-1/4" NPT Male	36515	130097-0269
		.125187" (F2 1/2")		5520	130098-0041
		F2 1/2" (.187250)		5522	130098-0046
		F2 1/2" (.250312)	1/2" NPT Male	5524	130098-0052
		F2 1/2" (.312375)		5526	130098-0061
		F2 1/2" (.312375)	1/2" NPT Male with O-ring	5526W	130098-0064
	Straight	F2 1/2" (.375437)	1/2" NPT Male	5528	130098-0069
		F2 1/2" (.375437)	/2" (.375437) 1/2" NPT Male with O-ring		130098-0071
		F2 1/2" (.375437)	Black Valox 1/2" NPT Male with O-ring	5528WBLK	130098-0072
		F2 1/2" (.437500)	1/2" NPT Male	5530	130098-0076
		F2 1/2" (.437500)	1/2" NPT Male with O-ring	5530W	130098-0078
MAX-LOC®	Right angle	F2 1/2" 90 body (.437500)		5531	130098-0080
	Charlant	F2 1/2" (.500562)	1 (OIL NIDT Made	5532	130098-0082
	Straight	F2 1/2" (.562625)	1/2" NPT Male	5534	130097-0327
	Right angle	F2 1/2" 90 body (.562625)		5535	130098-0093
		F3 3/4" (.437562)		5536	130098-0096
		F3 3/4" (.500625)	DIAN NOT MALE	5538	130098-0103
	Churcianlah	F3 3/4" (.562687)	3/4" NPT Male	5540	130098-0112
	Straight	F3 3/4" (.625750)		5542	130098-0118
		F4 1" (.687812)	TH NDT Mala	5554	1300980150
		F4 1" (.750875)	1" NPT Male	5556	1300980155
	Straight, oval UF cable	F2 1/2" (.218X .421)	1/2" NPT Male	5580	1300980185
	Single Eye, Closed Mesh	(.400560)		36564	130094-0493
Dura dana	Single Eye, Closed Mesh	(.530730)		36567	130094-0495
Bus-drop	Single Eye, Closed Mesh	(.700850)	N/A	36569	130094-0497
	Single Eye, Closed Mesh	(.960-1.250)	NA	36574	130094-0502
Bus-drop accessory	Bus-Drip Grip			36237	130099-0051
Liquid tiebt	Ctrointt	1/2 Male	Mala	36370	130096-0034
Liquid-tight	Straight	3/4 Male	Male	36371	130096-0036
	Charles Circ	.750990"		35032	130094-0234
Standard Duty	Straight, Single Eye, Closed Mesh,	1.250-1.490"	N/A	35034	1300940238
	Single Weave	1.750-1.990"		35036	1300940242



# **PORTABLE LIGHTING**

Туре	Description	Light Source	Watts	Voltage	Cord Length (feet)	Guard	Woodhead No.	Order No.
	1203 Q-Open with Ground Clip		100W		0.0		1203QOGC	130103-0038
	With cordset, outlet and switch		100W		25.0		402	130109-0007
		Incandescent	100W		50.0		405	130109-0009
	With cord, switch		100W		20.0	.,	WT3C-20	130109-0017
	With cord, switch, outlet		150W	120V		Yes	WT6C-25	130109-0026
			15W	-	25.0		1003-3	130108-0078
Hand lamp	With cord, switch, ballast	Fluorescent	1 2 1 4 /		25.0		1086-3	130108-0128
			13W				1083-3	130108-0106
	Wet Location Fluorescent Hand Lamp with Switch	Fluorescent	40W	120VAC 60 Hz			1940SA	130108-0183
	Rubber Hand Lamp with Receptacle						1175U	130102-0210
	Rubber Hand Lamp with Screw Release Reflector Guard with Switch and Side Outlet	Incandescent	100W	240V	25.0		106USA163	1301020117
	Industrial Duty Fluorescent Hand Lamp 27W	Fluorescent	27W	- 120VAC 60 Hz			1093-3	130108-0139
	Industrial Duty Fluorescent Hand Lamp 40W	ridorescent	40W	120 VAC 00 112			1097-3	130108-0144
	26W fluorescent haz duty handlamp		26W	120V	0.0		1090-HZ	130104-0021
Han dute	26W fluorescent haz duty handlamp with inline 12V transformer	Fluorescent	26W	12V	50.0		1090-HZ12IB163	130104-0026
Haz-duty handlamp	Haz duty handlamp, no cord		100W	120V	0.0	Yes	61430	130104-0041
	Haz-duty handlamp with 50 ft cord	Incandescent		1200	50.0		61430B163	130104-0045
	Haz duty handlamp with in-Line XFMR		75W	12V	30.0	30.0	1635-12B	130105-0046
	100', 14/2 SJTW		200W			Yes	5000	130111-0027
	Pro® Yellow Molded Stringlight, 14/2 SJTW						5030	130111-0044
	Flat 2-Wire, 12 Ga, 100' Stringlight with plastic guards		150W				302SRL	130111-0024
Ctringlight	Flat 2-Wire, 12 Ga, 100' Stringlight Canada with plastic	Incandescent	13000	120V	100.0	165	302SRLCA	130111-0026
Stringlight	Temporary light, 14/2 cord	incandescent		1200			202SRL	130111-0023
	12/3 Stringlight, Metal Guard						323126	130106-0107
	12/3 Stringlight, without Guard		200W			No	323123	130106-0104
	12/3 Stringlight, Metal Guard, 5 sockets				50.0	Yes	323526	130106-0115
	Pulse Start	Matal Isolata	400W		3.0		8575-MH-PS	130110-0052
Wide area light	Probe Start	Metal halide	70W	120V	10.0	Yes	8565-MH	130110-0035
	Twin tube, feed-through, 60 Hz	Fluorescent	64W		25.0		1351	130108-0164
Workstation	Four outlet low-volt XFMR workstation	N/A	200W	120V	6.0	N/A	1642-12	130105-0050
G., !	Clear Poly Guard	A1/A	N1/2	A1/A	NI/A	V.	381R	130112-0171
Guard	Polycarbonate Guard Only	N/A	N/A	N/A	N/A	Yes	STR101	130112-0246



### **PORTABLE LIGHTING**

Туре	Description	Light Source	Watts	Voltage	Cord Length (feet)	Guard	Woodhead No.	Order No.
General Duty Handlamp	Hand Lamp with Grips Molded and Switch	Fluorescent	13W	120VAC 60 Hz	20.0	Yes	WT3F-20	130109-0020
Wide area light	500W Halogen Floodlight	Quartz Halogen	500W	120VAC 60 Hz	25.0	Yes	8506	130135-0323
Machine Light	Halogen Machine Light with Magnet Base	Quartz Halogen	20W	120VAC	10.0	Yes	8540M	130110-0026
	Machine Light with Magnet Mount	Fluorescent	13W	120VAC 60 Hz	15.0		1083-3MM	130108-0120
Handle	Plain Rubber Handle and Socket	Incandescent	100W	240V	N/A	N/A	1173	130102-0204
Guard	Clear Poly Guard with bottom cover, 1.5" neck	N/A	N/A	N/A	N/A	Yes	382	130112-0172
Accessory	Watertite Socket with 4-1/2" leads	N/A	300W	600V	N/A	N/A	600	130152-0016
	Watertite Socket with 3-1/4" cover						601	130152-0020
	Watertite Lampholder 4-1/2" leads						603	130144-0094
	Turtle-Nek Socket with Mounting Flange for 3.5" or 4" boxes						606	130152-0021
	Socket Assembly for Super Safeway incandescent hand lamp	N/A	N/A	240V			1133	130112-0071
	Magnetic holder base with swivel	N/A	N/A	N/A			150	130112-0124
	1083-3 with switch (head only)	Fluorescent	13W	120VAC 60 Hz			1083-3HON	130112-0068