



Mechanical Dimensions: Inches [mm]



Part Numbers Information

Optifuse P/N	Current	Body Color
FMX-M-15A	15A	Gray
FMX-M-20A	20A	Blue
FMX-M-25A	25A	White
FMX-M-30A	30A	Pink
FMX-M-40A	40A	Green

Mounting Hole



Time vs. Percent of Rated Current

% of Rated Current	Min Hold Time	Max Hold Time
110%	4hr	-
135%	60s	1800s
200%	2s	60s
350%	200ms	7s
600%	40ms	1s

Electrical Specifications

Voltage Rating	58VDC
Interrupting Rating	1000A 58VDC
Operating Temperature	-40°F~260°F

Material Specifications

Body Material	Nylon with Fiberglass
Cover Material	Nylon 66
Insertion Force	45N Max.
Extraction Force	45N Min. / 35N Max.

Rev	Date of issue	Revision Notes
-----	---------------	----------------

Designed	Approved
----------	----------

A	05-20-2020	Initial Drawing	RC	OF
---	------------	-----------------	----	----