

Type FPK
UL Class M
Supplementary Protection
Fast Acting - 13/32"x 1-1/2"



www.optifuse.com

(619) 593-5050

For use as supplemental protection in general purpose and lighting applications.

Electrical:

600VAC – 100mA - 50A

600VDC – 100mA - 30A

Interrupt Ratings:

100,000A @ 600VAC (100mA – 30A)

10,000A @ 600VAC (35A – 50A)

100,000A @ 600VDC (100mA – 30A)

Supplementary Protection Only –

Not rated for branch circuit protection.

Agency Standards and Listings:




100mA-30A - UL Listed to Standard 248-14 File 33925

100mA-30A - CSA Certified Standard C22.2 No. 248.14

100mA-30A - DC listed to UL Standard 248-14

Mechanical Dimensions:



Part Number	Ampere Rating
FPK-100mA	100mA
FPK-125mA	125mA
FPK-143mA	143mA
FPK-200mA	200mA
FPK-250mA	250mA
FPK-500mA	500mA
FPK-750mA	750mA
FPK-1A	1A
FPK-1.5A	1.5A
FPK-2A	2A
FPK-3A	3A
FPK-4A	4A
FPK-5A	5A
FPK-6A	6A
FPK-7A	7A
FPK-8A	8A
FPK-10A	10A
FPK-12A	12A
FPK-15A	15A
FPK-20A	20A
FPK-25A	25A
FPK-30A	30A
FPK-30/35A	30/35*
FPK-30/40A	30/40*
FPK-30/50A	30/50*

* momentary in-rush capability

Warning:



-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of fuse with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.

Rev A 01/2008 - Page: 1/2
Code F02-01H

Type FPK
UL Class M
Supplementary Protection
Fast Acting - 13/32"x 1-1/2"



www.optifuse.com

(619) 593-5050

Time Current Curve Graphs

