Industrial Serial Card (CG1102-11920)



Specifications:

RS232

- One RS-232 serial port, 921.6 Kbaud maximum speed
- The RS232 interface on the industrial serial card is identical to the one on the low cost serial card. Please have a look at this <u>low cost serial card</u> for more info on the RS232 interface.

RS485

- One 22 KV isolated RS-485 serial port, 921.6 Kbaud maximum speed
- Connector: Examples of the connector you should use are:
 - Phoenix (MC 1,5/5ST-3,81)
 - Würth (691361300005)
- Termination switch: With this switch you can choose to terminate the RS485 network with a 120 Ohm resistor
- Wire selection: This switch allows you to use a 4 wire network or a 2 wire network

You can use the CloudGate in a 2 wire or 4-wire network.