



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™



PUNCH UNT-1-3/8" (POP)

Slug-Buster Knockout Punches 0.492 to 2.520

Cat No: 12304

UPC No: 783310123040

Description

- "The contractor's choice - worldwide
- Unique punch profile also splits slugs for easier slug removal
- Use with battery-powered, hydraulic, ratchet or manual drivers
- Uses standard Greenlee dies and draw studs
- Slug Buster punches available in sizes up thru 2.52" (64.0 mm)
- U.S. Patent #4,543,722 for Slug-Buster "

Specifications

- Application : For Punch Mild Steel, Aluminum, Fiberglass And Plastic
- Capacity Mild Steel : 10 GA (3.500 MM)
- Includes : Punch, Die And Draw Stud
- Operation Type : Battery, Hydraulic, Ratchet or Manual Drivers
- Replacement Part : 12303 UPC 12303 Punch, 12302 UPC 12302 Die And 04040 UPC 04040 Draw Stud
- Size : 1-3/8 IN (34.900 MM)
- Sub Brand : Slug-Buster
- Type : Knockout
- Weight : 1.100 LB (507.500 GM)