



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™

HOLESAW, VARIABLE PITCH (4 1/2) STD PK 20

Bi-Metal Hole Saws



Image  
Unavailable

Cat No: 825B-4-1/2

UPC No: 783310380511

### Description

---

- Cut through steel, tin, aluminum, fiberglass, wood and plastic
- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cutting through 2 IN x 4 IN wood studs
- Extra-tough bi-metal blade we use the highest grade of tool steel to outlast competitor's blades. That beats premature saw replacement and saves you money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longer life and better performance
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting
- Made in USA

### Specifications

---

- Application : For 4.000 Conduit IN
- Cutting Size : 1-5/8 IN
- D Chain : 4
- Hole Diameter : 4-1/2 IN
- Material : Bi-Metal
- Material Master Number : 50380516
- Package : 20/Standard Pack
- Type : Variable Pitch
- Use With Quick Change Arbor No. : 2801
- Use With Standard Arbor No. : 37156