

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT  bs  0 (g) pcs
JP75WP	0.35 (158.8)



## NOTES:

- 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
- 2. HOOK MATERIAL: PLATE MATERIAL: RIVET MATERIAL:

NYLON 6/6

PRE-GALVANIZED STEEL

ALUM I NUM

- 3. PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 3/4" (19.05) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 15 16s.
- 4. PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
- 5. PRODUCT MARKINGS:

cULus logo and statement:

"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."

ULC logo and statement:

"IN ACCORDANCE WITH CAN/ULC S-102.2 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING. FSR:0. SDC:20."

DIMENSIONS	ΙN	BRACKETS	ARF	METRIC	[ mr	m 1
DIMENSIONS	114		/ \i \ \			,, ,

CAD FILENAME/LAYERS

G03043BM\_PB\_JP75WP\_00



TINLEY PARK, ILLINOIS

J-PRO J-HOOK WITH PLATE FOR POWDER ACTUATED FASTENERS (JP75WP- )

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5\*

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

4 ft (1220mm) MIN. SPACING, FSR=0, SDC=20."								DRAWN BY JAD	MAT'L:	SCALE NO			
	R	4/8/05	JAD		INITIAL RELEASE	GB3043BM	R				DATE 1/5/06	SEE NOTE 2	DRAWING NO.
	REV	DATE	вч	СНК	DESCRIPTION	ECN -	R	CUST	SUP		CHK 'D		GB30

DRAWING NO.

GB3043BM

A

SIZE