


CABLE-D25SUB/B/S/ 50/KONFEK/S

Order No.: 2302120

The illustration shows a 15-position version

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2302120>Round shielded cable set, with 25-pos. D-SUB female and male
connectors, cable length: 0.5 m

Commercial data

GTIN (EAN)	 4 017918 893088
sales group	I682
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 270 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
02/05/2007

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Number of positions	25
Number of positions, control side	25
Number of connectors, control side	1
Number of positions, module side	25
Number of connectors, modul side	1
Fixed cable length	0.5 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	10.5 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Certificates / Approvals



Certification

CUL, GOST, UL

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;