

Housing - TG 40 - 2788896

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Housing for mounting surge voltage arresters

Product description


The TG 40 aluminum housing is equipped with two Pg13,5 cable screw connections positioned opposite each other on either side. The housing cover is attached to the base using four non-rusting and captive screws. TG 40 is supplied with DIN rail NS 35/7.5. On the DIN rail, five sections of 17.5 mm width each are available for the installation of protection devices. Degree of protection: IP65. IEC 529/EN 60529/DIN VDE 0470-1. Installation width 5 div.

Product Features

- For separate installation of surge protective devices
- Installation outdoors or indoors possible
- Use in harsh environmental conditions at the installation location
- Aluminum housing equipped with two cable glands
- The DIN rail requires five part width sections of 17.5 mm each



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 071950
Weight per Piece (excluding packing)	1704.7 GRM
Custom tariff number	76169910
Country of origin	Germany

Technical data

Dimensions

Width	120 mm
Height	160 mm
Depth	134 mm

Housing - TG 40 - 2788896

Technical data

Ambient conditions

Degree of protection	IP65
----------------------	------

General

Housing material	Aluminum
Color	gray

Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000899

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Drawings

Housing - TG 40 - 2788896

Dimensioned drawing

