


# RAD-CAB-LMR400-60

Order No.: 2867380

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867380>

Antenna extension cable, length: 60 ft

**Commercial data**

GTIN (EAN)	 4 017918 931759
Note	Made-to-order
sales group	H178
Pack	1 pcs.
Customs tariff	85442000
Catalog page information	Page 647 (IF-2009)

**Product notes**WEEE/RoHS-compliant since:  
07/01/2006

<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

**Technical data****General**

Connection 1	Plug connector connection
Type of connection	Type N (male)
Fixed cable length	18 m
Cable type	LMR-400
Cable, attenuation	0.13 dB/m

Minimum bending radius	25.00 mm
External diameter	10.00 mm
Outer sheath, material	PE
Connection name	Plug connector connection
Type of connection	Type N (male)
Note	Both sides
Ambient temperature (operation)	-40 °C ... 85 °C

**Address**

PHOENIX CONTACT Deutschland GmbH  
Flachmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 12000  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact  
Technical modifications reserved;