

E-Box M12, 1 pushbutton high red, 1 pushbutton flat green, illuminated

1.22.251.242/3502



General information

Color of housing cap grey

Dimensions

Dimensions 123,2 mm x 40 mm, height depending on actuators used

Mechanical design

Mounting	with clip in 40 mm aluminum rails
Connection	M12
Plug M12	8-pin
Actuator 1	Pushbutton protruding red, symbol "0" (1NC); 1NC: 3-4
LED actuator 1	LED red; 7-8
Actuator 2	Pushbutton flat green symbol "I" (1NO); 1NO: 1-2
LED actuator 2	LED green; 5-6

Electrical characteristics

Operating current min.	1 mA
Operating current max.	100 mA
Rated power max.	250 mW

Other specifications

Protection as per EN 60529	IP65
Protection class	II
Operating temperature min.	-25 °C
Operating temperature max.	+70 °C
Operating life / B10	depending on actuators used
ROHS compliant	yes
REACH compliant	yes

