

RAFIX 16 F - Signal indicator, flush lens, collar metallized, round

1.65.126.011/1500



General information	
Form of lens	flat lens
Color of lens	transparent green
Form of collar	round
Color of collar	silver metallic
.	
Dimensions	
Collar dimensions	ø 28 mm
Overall height	1.9 mm
Mounting depth with contact block	50 mm
Key grid	30 x 30 mm
Mounting hole	ø 22.3 mm
Mechanical design	
Mounting	ring nut
Contact function	.
Illumination	yes
Other specifications	
Operating life (operations)	- cycle
Degree of protection from front side	IP65 (DIN EN 60529)
Operation temperature min.	-25 °C
Ambient temp. operating max. without lamp /	
LED	<u>- °C</u>
Ambient temp. operating max. with lamp /LED	+55 °C
Storage temperature min.	-40 °C
Storage temperature max.	+85 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
ROHS compliant	yes
REACH compliant	yes

Panel cut-out to IEC 60947-5-1





