




3:2

NOTES :

HOLE SIZE : 7.84 / 8

PANEL THICKNESS RANGE : 0.5 / 3.55

SCREW SIZE : #8-#10

UNLESS OTHERWISE STATED


ALL DIMENSIONS IN mm

DO NOT SCALE

LINEAR TOLERANCE

SIZE	(0)	(0.0)	(0.00)
0-10mm	±0.5	±0.15	±0.10
>10-30	±0.5	±0.20	±0.15
>30-50	±0.5	±0.30	±0.20
>50-100	±0.8	±0.50	±0.25
>100-200	±1.5	±0.80	±0.40
>200-300	±2.0	±1.20	±0.80
>300-500	±3.0	±2.00	±1.00
>500	±5.0	±3.00	±1.50

THIRD ANGLE PROJECTION



ANGULAR TOLERANCE ±0.5 DEGREES
UNSPECIFIED RADII 0.25mm
DRAFT ANGLE 0.5 DEGREES
DIMENSIONS IN BRACKETS [] ARE
IN INCHES FOR REFERENCE ONLY

ORG. SCALE: 3:1

CREATE DATE: 11/12/2018

MATERIAL: PA 66

Part ID: 1456144

Project: P160230-1

TITLE:

SQ CLOSED SCREW
GROMMET NUT H0.79

DWG. No.

60SGC00005

SHEET
1 of 1
ISSUE
1

APPROVED - UNCONTROLLED