



PART NO.	DIM. "A"
MSPMST-2-01	1/8 [3.2]
MSPMST-3-01	3/16 [4.8]
MSPMST-4-01	1/4 [6.4]
MSPMST-5-01	5/16 [7.9]
MSPMST-6-01	3/8 [9.5]
MSPMST-7-01	7/16 [11.1]
MSPMST-8-01	1/2 [12.7]
MSPMST-9-01	9/16 [14.3]
MSPMST-10-01	5/8 [15.9]

TO SNAP-FIT IN A $.125 \pm .002$ [3.18 ± 0.05] DIA. HOLE, IN A $.062$ [1.57] THICK BOARD



TO SELF-THREAD INTO A #4 OR M3 THREADED HOLE, WITH $.063$ [1.6] MINIMUM ENGAGEMENT



NOTES:
 1. MATERIAL: NYLON 6/6 (RMS-01).
 2. COLOR: NATURAL.

A	RELEASED FOR PRODUCTION	SM 08/10/04
R E V	DESCRIPTION	ENGR. DATE

TITLE: **MINI SUPPORT POST, MICRO, SELF-THREADING**



CREATED USING SOLIDWORKS	FILE #: MSPMST	DWN: SM/RT	APP: RT	PRELIMINARY
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 2	SHEET SIZE: A	DT: 06/30/04	CHKD: RDG
RE: RICHCO, INC.	RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		PART # SEE TABLE	PRINT TYPE CA